

Digital non-glass pH sensor Memosens CPS47E

Memosens 2.0 ISFET pH electrode for the chemical, life sciences and food industries



Více informací a současné ceny:

www.cz.endress.com/CPS47E

Výhody:

- **IIoT ready:** Memosens 2.0 offers extended storage of calibration and process data, enabling better trend identification and providing a future-proof basis for predictive maintenance and enhanced IIoT services.
- **Unbreakable:** Non-glass PEEK body ensures highest product safety where glass breakage is intolerable.
- **Resistant to poisoning:** Constant refilling of KCl bridge electrolyte and separate reference lead prevent poisoning ions from entering the electrode.
- **The sensor is suitable for autoclaving and sterilization with hot steam** offering long-term stable measurement.
- **Low maintenance:** ISFET technology is insensitive to temperature changes enabling long calibration intervals
- **Maximum process safety:** Thanks to non-contact, inductive signal transmission, problems with moisture are a thing of the past.
- **Reduced operating costs:** Laboratory calibration and fast sensor exchange on-site minimize process downtime and extend sensor lifetime

Souhrn technické specifikace

- **Rozsah měření** pH 0 to 14
- **Procesní teplota** -15 to 135 °C (5 to 275 °F)
- **Procesní tlak** Max. 11 bar abs at 100 °C (max. 160 psi at 212 °F)

Oblast použití: Memosens CPS47E is the high performer with liquid KCl reference for media with low conductivity or high organic load. It measures accurately even in applications with fast-changing media. Its unbreakable shaft ensures best product safety. Thanks to Memosens 2.0

digital technology, the pH sensor resists moisture and enables lab calibration, increasing process safety and simplifying operation. Its extended storage of calibration and process data provides a perfect basis for predictive maintenance.

Technické informace

pH

Měřicí princip

ISFET

Aplikace

For applications requiring high accuracy in blocking media or high content of organic solvents

Charakteristika

Digital, sterilizable and autoclavable pH electrodes for hygienic production processes with KCl vessel for measuring in media with low conductivity

Reference

Liquid KCl

Rozsah měření

pH 0 to 14

Princip měření

Princip měření

Provedení

Provedení

Materiál

Sensor shaft: PEEK

Sealings: FFKM

Metal lead: Ag/AgCl

Open aperture: Ceramic junction, zirconium dioxide

O-ring: FKM

Process coupling: PPS fiber-glass reinforced

Nameplate: Ceramic metal oxide

pH

Rozměr

Diameter: 12 mm (0.47 inch)
Shaft lengths: 120, 225 and 360 mm
(4.72, 8.86 and 14.17 inch)

Procesní teplota

-15 to 135 °C (5 to 275 °F)

Procesní tlak

Max. 11 bar abs at 100 °C (max. 160 psi at 212 °F)

Teplotní čidlo

Pt1000

Certifikace pro prostředí s nebezpečím výbuchu

With the following approvals for use in potentially explosive areas of Zone 0, Zone 1 and Zone 2: ATEX, IECEx, CSA C / US, NEPSI, JPN Ex, INMETRO, UKCA and Korea Ex

Připojení

Inductive, contactless connection head with Memosens 2.0 technology

Krytí

IP 68

Více informací www.cz.endress.com/CPS47E