

## RN221N

### Active barrier with optional HART® diagnosis

Active barrier with power supply for safe separation of 4...20 mA current circuits



from **CZK3,704.00**

Price as of 17.10.2021

More information and current pricing:

[www.cz.endress.com/RN221N](http://www.cz.endress.com/RN221N)

#### Benefits:

- Wide range power supply, flexible power source
- Compact side by side DIN rail housing
- International Ex approvals; marine approval
- Bidirectional HART® transmission. Communication sockets for HART® sensor setting up. Evaluation of status information from connected transmitter with HART® protocol.
- Primary or secondary master operating mode, automatic selection
- Sensor monitoring with early-warning system
- Manual or automatic reset of the relay contact

#### Specs at a glance

- **Input** 1 x analog 4...20 mA
- **Output** 1 x analog 4...20 mA

**Field of application:** The active barrier RN221N supplies e.g. a transmitter with power, if required also in the Ex-area, and then transmits the galvanically isolated signal. With the optionally available HART® monitoring the status of the transmitter is monitored. If an error arises a relay at the RN221N sends an alarm. The relay has to be actively set back. Thus even just briefly occurring errors can be easily located.

#### Features and specifications

Power supplies & barrier

**Measuring principle**

Active barrier

---

**Power supplies & barrier****Measuring principle**Power supply

---

**Function**Active barrier with power supply for safe separation of 4...20 mA current circuit

---

**Loop power supply**20...250 V DC/AC

---

**Auxiliary power supply / Loop power supply**20...250 V DC/AC

---

**Input**1 x analog 4...20 mA

---

**Output**1 x analog 4...20 mA

---

**Certificates**

ATEX (Ex ia)

FM AIS

CSA (Ex ia)

IECEX (Ex ia)

NEPSI (Ex ia)

JPN (Ex ia)

Non-hazardous area + EAC marking

EAC (Ex ia)

---

**Operation**HART

---

## Acquisition / Evaluation

**Measuring principle**

Power supply

**Function**

Active barrier with power supply for safe separation of 4...20 mA current circuit

**Certification**

ATEX II(1)GD(Ex ia)IIC

FM USA IS

FM USA NI

CSA IS

CSA NI

IECEX Ex ia

TIIS Ex ia

GOST Ex i

Marine approval

SIL

Hygenic WHG

**Input**

1 x analog 4...20 mA

**Output**

1 x analog 4...20 mA

**Relay output**

1 x no contact

Acquisition / Evaluation

---

**Auxiliary power supply / Loop power supply**  
20...250 V DC/AC

---

**Dimensions (wxhxd)**  
22.5 x 110 x 112 mm  
  
(0.89" x 4.33" x 4.41")

---

**Operation**  
HART

---

More information [www.cz.endress.com/RN221N](http://www.cz.endress.com/RN221N)