

# Flow assembly Flowfit CPA240

Durable assembly for the chemical,  
petrochemical, and power industries



More information and current pricing:

[www.cz.endress.com/CPA240](http://www.cz.endress.com/CPA240)

## Benefits:

- Simple installation and removal of the electrode holder (e.g. for calibration)
- Flexible connection to the process by means of various connectors and installation versions
- Less condensation due to a Goretex filter
- Reduces installation effort by providing 3 mounting positions for 120 mm sensors or an optional cleaning unit

## Specs at a glance

- **Process temperature** PVDF version: 0 to 120 °C (32 to 248 °F)  
Stainless steel version: -15 to 150 °C (5 to 302 °F) With EPDM:  
-15 to 140 °C (5 to 284 °F)
- **Process pressure** PVDF version: max. 8 bar at 50 °C (max. 116 psi  
at 122 °F) Stainless steel version: max. 10 bar (max. 145 psi)

**Field of application:** The Flowfit CPA240 flow assembly is designed for all demanding applications where high temperatures and pressures are involved. With its various connections, Flowfit flexibly adapts to your process offering space for three sensors. Simple installation and removal of the sensors save time for maintenance and recalibration.

## Features and specifications

ORP / Redox

### Measuring principle

Sensor ORP / Redox

---

**ORP / Redox****Application**

Drinking water treatment plants, boiler feedwater and ultra-pure water plants, cooling-water circuits, fertiliser production, sugar production, gas scrubbers, petrochemical plants

---

**Installation**

Flow through holder

---

**Characteristic**

Piping, bypass

---

**Design**

3 electrode installation locations, 120mm electrodes, flow direction horizontal or from the bottom, thread connection G1/2" for spray cleaning

---

**Material**

Flow vessel: PVDF or stainless steel 1.4404  
O-rings: EPDM, Viton, Chemraz or Fluoraz

---

**Process temperature**

PVDF version: 0 to 120 °C (32 to 248 °F)  
Stainless steel version: -15 to 150 °C (5 to 302 °F)  
With EPDM: -15 to 140 °C (5 to 284 °F)

---

**Process pressure**

PVDF version: max. 8 bar at 50 °C (max. 116 psi at 122 °F)  
Stainless steel version: max. 10 bar (max. 145 psi)

---

**Connection**

Pressurized flange DN25/PN16, ASME 1" lbs 150, JIS 10K25A

---

**Additional certifications**

Material certification 3.1.B EN 10204

---

**pH****Measuring principle**

Potentiometric

---

pH

**Application**

Drinking water treatment plants, boiler feedwater and ultra-pure water plants, cooling-water circuits, fertiliser production, sugar production, gas scrubbers, petrochemical plants

**Installation**

Flow assembly

**Characteristic**

Piping, bypass

**Design**

3 electrode installation locations, 120mm electrodes, flow direction horizontal or from the bottom, thread connection G1/2" for spray cleaning

**Material**

Flow vessel: PVDF or stainless steel 1.4404  
O-rings: EPDM, Viton, Chemraz or Fluoraz

**Process temperature**

PVDF version: 0 to 120 °C (32 to 248 °F)  
Stainless steel version: -15 to 150 °C (5 to 302 °F)  
With EPDM: -15 to 140 °C (5 to 284 °F)

**Process pressure**

PVDF version: max. 8 bar at 50 °C (max. 116 psi at 122 °F)  
Stainless steel version: max. 10 bar (max. 145 psi)

**Connection**

Pressurized flange DN25/PN16, ASME 1" lbs 150, JIS 10K25A

**Additional certifications**

Material certification 3.1.B EN 10204

More information [www.cz.endress.com/CPA240](http://www.cz.endress.com/CPA240)