

Radiometric Level/density measurement Source Container FQG62

Radiation source container with source holder for manual or pneumatic switch-on/switch-off



More information and current pricing:

www.de.endress.com/FQG62

Benefits:

- High safety level thanks to highest classification for the source supplied (DIN 25426/ISO 2919, typically classification C66646) and safe and easy source replacement
- Reliable measurement due to lightweight container and almost spherical design which provides optimized screening
- Compact, easy-to-mount device with the possibility of various angles of emission for optimum adaptation to the application
- Manual or pneumatic switching on/off and padlock, cylinder lock or locking bolt for fixing the switching position
- Switch status easily identified

Specs at a glance

- **Process temperature** Any
- **Process pressure / max. overpressure limit** Any
- **Main wetted parts** Non-contact

Field of application: The FQG62 source container is designed to hold the radioactive source during radiometric point level detection, continuous level and density measurement. The radiation is emitted almost unattenuated in one direction only, and is damped in all other directions. This guarantees highest safety for the personnel and a reliable measurement.

Features and specifications

Continuous / Liquids**Measuring principle**Radiometric

Characteristic / Application

Source container

Emission angle: 40 / 20 degrees

Approximately 87kg

SpecialitiesManual or pneumatic switch-on/ switch-off

Ambient temperature

-40 °C...+200 °C

(-40 °F...+392 °F)

Process temperatureAny

Process pressure / max. overpressure limitAny

Main wetted partsNon-contact

Process connectionNon-contact

Certificates / ApprovalsATEX, GOST

Continuous / Solids**Measuring principle**Radiometric

Continuous / Solids**Characteristic / Application**

Source container
Emission angle: 40 / 20 degrees
Approximately 87kg

Specialities

Control area calculation with
Applicator

Ambient temperature

-40 °C...+200 °C
(-40 °F ...+392 °F)

Process temperature

Any

Process pressure / max. overpressure limit

Any

Main wetted parts

Non-contact

Process connection

Non-contact

Certificates / Approvals

ATEX, GOST

Point Level / Liquids**Measuring principle**

Radiometric Limit

Characteristic / Application

Source container
Emission angle: 5 degrees
Approximately 87kg

Point Level / Liquids**Specialities**

Control area calculation with
Applicator

Ambient temperature

-40 °C...+200 °C
(-40 °F...+392 °F)

Process temperature

Any

Process pressure / max. overpressure limit

Any

Main wetted parts

Non-contact

Process connection

Non-contact

Certificates / Approvals

ATEX, GOST

Point Level / Solids**Measuring principle**

Radiometric Limit

Characteristic / Application

Source container
Emission angle: 5 degrees
Approximately 87kg

Specialities

Control area calculation with
Applicator

Point Level / Solids**Ambient temperature**

-40 °C...+200 °C
(-40 °F...+392 °F)

Process temperature

Any

Process pressure / max. overpressure limit

Any

Main wetted parts

Non-contact

Process connection

Non-contact

Certificates / Approvals

ATEX, GOST

Density**Measuring principle**

Radiometric Density

Characteristic / Application

Source container
Emission angle: 5/ 20/ 40 degrees
87kg

Ambient temperature

-20 °C...+200 °C
(-40 °F...+392 °F)

Process temperature

Any

Process pressure

Any

Density

Wetted parts

Non-contact

Hygienic

Non-contact

Specialities

Control area calculation with
Applicator

More information www.de.endress.com/FQG62