

Memograph M RSG40



Yderligere oplysninger og aktuel pris::

www.dk.endress.com/RSG40

Fordele:

- Visual: 7" TFT display as onsite display for optimum readability
- Secure: Security package with person-specific access authorization and electronic signature (FDA 21 CFR 11)
- Flexible: Free choice of display mode. E.g. instrument, process screen and circular chart display
- Clear: Alarm management with all active, confirmed and historical alarms
- Practicable: Installation depth 158 mm, front-panel IP65, NEMA4; Operating via external USB keyboard, printout via USB printer
- Limitless: Integrated Web server, fieldbus (Profibus, Modbus), common standard protocols and interfaces such as USB, TCP/IP, OPC and Ethernet are supported
- Informative: Event search, automatic signal analysis

Oversigt over specifikationer

- **Input** 20 analog (max) (U, I, TC, RTD, frequency, pulse) 14 digital (max) (control, event and counting inputs)
- **Output** 12 relays (max) 2 analog output (max) (I, pulse) 1 loop power supply
- **Display** TFT 7" colour graphic display
- **Power supply** 100...230 V AC +/-10% 24V (-10%; +15%) AC/DC
- **Storage/Recording** Internal memory SD card USB Stick

Anvendelsesområde: Safe and complete recording and visualization of all process sequences. The Memograph M RSG40 has a wide range of functionality, modular construction and an intuitive operator concept. With its brilliant 7" TFT display it is possible to display process values e.g. as curves, as a circular chart display or as an application-specific process screen. The Memograph M offer is completed with specific application packages. Memograph M - More than just a videographic recorder!

Funktioner og specifikationer

Data Manager & Data Logger**Measuring principle**Data manager

Measuring principleAdvanced Graphic Data Manager

Function

The versatile solution with secure data recording, visualization and application-specific software packages.

Input

20 analog (max) (U, I, TC, RTD, frequency, pulse)

14 digital (max) (control, event and counting inputs)

Output

12 relays (max)

2 analog output (max) (I, pulse)

1 loop power supply

Interface

RS232/485

Ethernet

USB

Modbus RTU/TCP Slave

Modbus RTU Master

PROFIBUS DP

Storage/Recording

internal memory

SD card

USB flash drive

DisplayTFT 7" colour graphic display

Housing

panel mounting

desktop housing

field housing

Data Manager & Data Logger

Certificates

21 CFR Part 11
 Milk pasteurisation approval
 UL recognized
 CSA

Software package

Batch software
 Waster water software
 Tele-alarm software
 Gas-steam-heat calculation
 Energy software (water + steam)
 Waste water + storm overflow + Tele Alarm
 Tele-alarm software + energy software (water + steam)

Energy & Application Manager

Measuring principle

Application manager

Measuring principle

Energy manager

Function

Mass flow and energy calculation for Water and Steam.

Calculations

Not defined

Number of applications

Not defined

Data storage

yes

Calculation standards

Not defined

Energy & Application Manager **Communication**Not defined

Power supplyNot defined

Loop power supply24...28 V DC

Protection classIP30

Input

4...20 universal

6...14 digital

Output2 analog

Dimensions (WxHxD)195.2 x 149.2 x 227.1 mm (7.69" x 5.87" x 8.94")

OperationJog shuttle on site and PC software ReadWin

DisplayWide-screen TFT

Software functionsInternal calculation for mass flow and energy

Certificates

CE

EAC

UL (US and CA)

Thermal Energy Measurement **Measuring principle**
Electronic Data Acquisition

Function

Mass flow and energy calculation for Water and Steam.

Certification

CE,
EAC,
UL (US and CA)

Input

4...20 universal, 6...14 digital

Output

2 analog

Relay output

6...12

Auxiliary power supply

24...28 V DC

Dimensions (wxhxd)

195.2 x 149.2 x 227.1 mm
(7.69" x 5.87" x 8.94")

Software

Internal calculation for mass flow and energy

Operation

Jog shuttle on site and PC software ReadWin

Display

Wide-screen TFT

Others

Memory inside, balancing

Data Acquisition

Measuring principle

Electronic Data Acquisition

Functions

Signal analysis
Interface / modem
OPC-Server
ReadWin 2000
Mathematic formula editor
energy package, water+steam

Maximal input

20 analog (U, I, TC, RTD, Frequency, Pulse)
14 digital (control, event and counting inputs)

Maximal output

12 Relay
2 Analog output (I, Pulse)
1 Power loop supply

Interface

RS 232
RS 485
Ethernet
Modbus RTU
Modbus TCP
PROFIBUS DP
USB

Storage/Recording

Internal memory
SD card
USB Stick

Display

TFT 7" colour graphic display

Data Acquisition

Housing

panel mounting
desktop housing
Field housing

Power supply

100...230 V AC +/- 10%
24V (-10%; +15%) AC/DC

Certification

21 CFR 11
Milk pasteurisation approval
UL recognized
CSA GP

Software package

Batch programme
Waster water software
Tele-Alarm software
Gas-Steam-Heat calculation
Energy package + Water + Steam
Waste water + Storm overflow + Tele Alarm
Tele-Alarm software + Energy package + Water +
Steam

Yderligere information www.dk.endress.com/RSG40