

# RTD Thermometer TST410



Yderligere oplysninger og aktuel pris::

[www.dk.endress.com/TST410](http://www.dk.endress.com/TST410)

## Fordele:

- High degree of flexibility thanks to modular design with standard terminal heads as per DIN EN 50446 and customer-specific immersion lengths
- High degree of insert compatibility and design as per DIN 43772
- High accuracy and exceptional long-term stability

## Oversigt over specifikationer

- **Accuracy** class A acc. to IEC 60751 class B acc. to IEC 60751
- **Response time**  $t_{50} = 2 \text{ s}$   $t_{90} = 4 \text{ s}$
- **Max. process pressure (static)** at 20 °C: 40 bar (580 psi)
- **Operating temperature range** PT 100: -50 °C ...400 °C (-58 °F ...752 °F)
- **Max. immersion length on request** up to 10.000,00 mm (393,70")

**Anvendelsesområde:** The thermometer is mainly used in the chemical industry but also finds its use in other branches. Typical applications are pressure-less systems such as air ducts, flues and pipelines. For protection against high industrial demands the use of a special protective sleeve is recommended. A variety of dimensions offers flexible application possibilities.

## Funktioner og specifikationer

Thermometer

Measuring principle

---

**Thermometer****Characteristic / Application**

metric style  
modular temperature assembly  
process connection as compression fitting  
without neck  
mini-head

---

**Thermowell / protection tube**

without (not intended to use with thermowell)

---

**Insert / probe**

mineral insulated (MI), flexible

---

**Outer diameter protection tube / Insert**

3,0 mm (0,12")

---

**Max. immersion length on request**

up to 10.000,00 mm (393,70" )

---

**Material protection tube/ thermowell**

1.4401 (316)

---

**Process connection**

compression fitting:  
G1/4"

---

**Tip shape**

straight

---

**Operating temperature range**

PT 100:  
-50 °C ...400 °C  
(-58 °F ...752 °F)

---

**Max. process pressure (static)**

at 20 °C: 40 bar (580 psi)

---

## Thermometer

### Accuracy

class A acc. to IEC 60751

class B acc. to IEC 60751

---

### Response time

t<sub>50</sub> = 2 s

t<sub>90</sub> = 4 s

---

### Integration head transmitter

no

---

Yderligere information [www.dk.endress.com/TST410](http://www.dk.endress.com/TST410)