

Ultrasonic measurement Time-of-Flight Prosonic FDU90

Ultrasonic sensor for level and flow measurement for connection to FMU9x (measuring range up to 3m)



Fordele:

- Integrated temperature sensor for Time-of-Flight correction. Accurate measurements are possible, even if temperature changes are present
- Hermetically welded PVDF sensor for highest chemical resistance
- Suited for rough ambient conditions thanks to separate installation from the transmitter (up to 300m)
- Reduced build-up formation because of the self-cleaning effect
- Integrated automatic sensor detection for transmitters FMU90 / FMU95 for simple commissioning
- Weather resistant and flood-proof (IP 68)
- Integrated heating against a build-up of ice at the sensor (optional) ensures reliable measurement

Yderligere oplysninger og aktuel pris::

www.dk.endress.com/FDU90

Oversigt over specifikationer

- **Process temperature** -40 °C ... 80 °C (-40 °F ... 176 °F)
- **Process pressure / max. overpressure limit** 0.7 bar ... 4 bar abs (10 psi ... 58 psi)
- **Max. measurement distance** Liquids: 3 m (9.8 ft), Solids: 1.2 m (3.9 ft)
- **Accuracy** +/- 2mm + 0.17% of measured distance
- **Main wetted parts** PVDF (IP68 / NEMA6P)

Anvendelsesområde: The FDU90 ultrasonic sensor for continuous, non-contact and maintenance-free level measurement of fluids, pastes, sludges and powdery to coarse bulk materials. But also for flow measurement in open channels and measuring weirs. The measurement

is unaffected by dielectric constant, density or humidity and also unaffected by build-up due to the self-cleaning effect of sensors. Suited for explosion hazardous areas. Maximum measuring range in liquids 3m (9.8ft), solids 1.2m (3.9ft).

Funktioner og specifikationer

Continuous / Liquids

Measuring principle

Ultrasonic

Characteristic / Application

Separated version with field housing or top hat rail housing for control cabinet instrumentation, 300m in-between sensor and transmitter

Specialities

Floating protection tube

Supply / Communication

4-wire (HART, Profibus DP)

Accuracy

+/- 2mm + 0.17% of measured distance

Ambient temperature

-40 °C ... 80 °C
(-40 °F ... 176 °F)

Process temperature

-40 °C ... 80 °C
(-40 °F ... 176 °F)

Process pressure / max. overpressure limit

0.7 bar ... 4 bar abs
(10 psi ... 58 psi)

Main wetted parts

PVDF (IP68 / NEMA6P)

Continuous / Liquids

Process connection

Front side thread:

G / NPT 1 1/2"

Rear side thread:

G / NPT 1"

Ceiling mounting

Blocking distance

0.07 m (0.23 ft)

Max. measurement distance

Liquids: 3 m (9.8 ft),

Solids: 1.2 m (3.9 ft)

Communication

Transmitter:

4 ... 20 mA HART

Profibus DP

Certificates / Approvals

ATEX, FM, CSA, IEC Ex, INMETRO, NEPSI, EAC Ex

Options

Second 4...20mA output

Components

Transmitter:

FMU90, FMU95

Application limits

Foam / high turbulence possible:

FDU92

Flange-flush assembly:

FDU91F

For tank farms scanner:

FMU95

Continuous / Solids**Measuring principle**Ultrasonic

Characteristic / ApplicationSeparated version with field housing or top hat rail housing for control cabinet instrumentation, 300m in-between sensor and transmitter

Supply / Communication4-wire (HART, PROFIBUS DP)

Accuracy+/- 2mm + 0.17% of measured distance

Ambient temperature-40 °C ... 80 °C
(-40 °F ... 176 °F)

Process temperature-40 °C ... 80 °C
(-40 °F ... 176 °F)

Process pressure / max. overpressure limit0.7 bar ... 4 bar abs
(10 psi ... 58 psi)

Main wetted partsPVDF (IP68 / NEMA6P)

Process connectionFront side thread:
G / NPT 1 1/2"
Rear side thread:
G / NPT 1"
Ceiling mounting

Blocking distance0.07 m (0.23 ft)

Continuous / Solids

Max. measurement distance

Liquids: 3 m (9.8 ft),
Solids: 1.2 m (3.9 ft)

Communication

Transmitter:
4 ... 20 mA HART
Profibus DP

Certificates / Approvals

ATEX, FM, CSA, IEC Ex, INMETRO, NEPSI, EAC Ex

Options

Second 4...20mA output

Components

Transmitter:
FMU90

Liquids

Measuring principle

Ultrasonic

Product headline

Version with separate transmitter in field housing or top hat rail housing
Cost effective solution for open channel flow measurement in water /
wastewater plants

Max. measurement error

accuracy:
distance measurement: +/- 2mm + 0.17%
resolution:
distance measurement: 1m

Measuring range

max measuring distance up to 3 m / 9.8 ft

Liquids

Max. process pressure

atm.

Medium temperature range

-40 °C ... 80 °C

(-40 °F ... 176 °F)

Degree of protection

IP68

Display/Operation

Transmitter

Outputs

Transmitter:

4 ... 20 mA HART

PROFIBUS DP

Inputs

Transmitter

Digital communication

HART, PROFIBUS DP

Hazardous area approvals

ATEX, FM, CSA, IEC Ex, INMETRO, NEPSI, EAC Ex

Yderligere information www.dk.endress.com/FDU90