

Hydrostatic Level measurement Waterpilot FMX11

Simple and reliable level probe for freshwater applications



Fordele:

- Simple and reliable transmitter for various drinking water applications
- Easy installation, commissioning and operation
- Orderable with flexible measuring ranges and cable lengths tailored to fit your application
- Robust construction for durable long-term services
- Suitable for surface water monitoring in rivers and lakes as well as level monitoring for drinking water production, e.g. in water towers, dams, gauging stations
- Compact size $d=22\text{mm}$ (0.87"), makes this an excellent choice for applications in bore holes and small diameter stilling wells.
- Simple specification and ordering

fra **2.780,00 kr.**

Pris pr. 25.07.2021

Yderligere oplysninger og aktuel pris::

www.dk.endress.com/FMX11

Oversigt over specifikationer

- **Accuracy** $p_n \geq 400\text{mbar}$: 0.35 % $p_n < 400\text{mbar}$: 0.50 %
- **Process temperature** $-10^\circ\text{C} \dots +70^\circ\text{C}$ ($+14^\circ\text{F} \dots +158^\circ\text{F}$)
- **Pressure measuring range** 200 mbar...2 bar (3 psi...29 psi)
- **Process pressure absolute / max. overpressure limit** 10 bar (145 psi)
- **Main wetted parts** 316L

Anvendelsesområde: The Waterpilot FMX11 transmitter is typically used in environmental applications for hydrostatic level measurement. It is certified for drinking water applications and can be used in wells, storage tanks, water towers, dams, gauging stations, lakes and rivers.

Funktioner og specifikationer

Pressure**Measuring principle**Hydrostatic pressure

Characteristic

Compact probe with metallic cell for hydrostatic level measurement

in fresh water, ground water and potable water storage.

Supply voltage8...28 VDC

Reference Accuracypn \geq 400mbar: 0.35 %pn < 400mbar: 0.50 %

Long term stability0.1 % of URL/year

Process temperature

-10°C...+70°C

(+14°F...+158°F)

Ambient temperature

-10°C...+70°C

(+14°F...+158°F)

Measuring cell

200 mbar...2 bar

(3 psi...29 psi)

Process connection

Suspension clamp

Cable mounting screws

Pressure**Material process membrane**

Metal

Communication

4...20 mA

Drinking water approvals

NSF, KTW, ACS

Continuous / Liquids**Measuring principle**

Hydrostatic

Characteristic / Application

Compact probe with metallic cell for hydrostatic level measurement

in fresh water, ground water and potable water storage.

Supply / Communication

8...28 VDC

Accuracy

$p_n \geq 400\text{mbar}$: 0.35 %

$p_n < 400\text{mbar}$: 0.50 %

Long term stability

0.1% of URL/year

Ambient temperature

-10°C...+70°C

(+14°F...+158°F)

Continuous / Liquids

Process temperature

-10°C...+70°C

(+14°F...+158°F)

Process pressure absolute / max. overpressure limit

10 bar (145 psi)

Pressure measuring range

200 mbar...2 bar

(3 psi...29 psi)

Main wetted parts

316L

Process connection

Suspension clamp

Cable mounting screws

Max. measurement distance200 m H₂O(656 ft H₂O)**Communication**

4...20 mA

Drinking water approvals

NSF, KTW, ACS

Yderligere information www.dk.endress.com/FMX11