


## Micropilot M FMR250



More information and current pricing:

[www.dk.endress.com/FMR250](http://www.dk.endress.com/FMR250)

### Benefits:

- Non-contact measurement: Measurement is almost independent from product properties
- 2-wire technology, low price: A real alternative to differential pressure, floats and displacers.  
2-wire technology reduces wiring costs and allows easy implementation into existing systems
- Easy commissioning, documentation and diagnostics via Endress+Hauser operating software
- Easy on-site operation via menu-driven alphanumeric display
- Used for level monitoring (MIN, MAX) up to SIL2 as per IEC 61508/ IEC 61511-1
- HART or PROFIBUS PA respectively FOUNDATION Fieldbus protocol
- Max. measuring range 70m (230ft)

### Specs at a glance

- **Accuracy** +/- 15mm (or 0.04% of range, whatever is larger)
- **Process temperature** -40 °C...+200 °C (-40 °F...+392 °F)
- **Process pressure / max. overpressure limit** Vacuum...16bar (Vacuum...232psi)
- **Max. measurement distance** 70 m (230 ft)
- **Main wetted parts** PEEK, 1.4435, 1.4404, 316L

**Field of application:** The Micropilot FMR250 is ideally suited for tall silos and high temperature requirements also as for abrasive solids. The FMR250 has a integrated air purge connection for extremely dusty conditions or media tending to create build-up. Micropilot FMR250 performs continuous, non-contact level measurement especially in powdery to granular bulk solids. Dust, filling noises, temperature layers and gas stratification do not affect measurement.

### Features and specifications

---

**Continuous / Solids****Measuring principle**

---

**Characteristic / Application**

Non-contact level measurement especially in powdery to granular bulk solids. Level measurement in tall silos with extremely dusty bulk solids e.g. cement, raw meal or animal feed. Applications with highly abrasive bulk solids e.g. ferrite / clinker

---

**Specialities**

Air purge connection

---

**Supply / Communication**

2-wire (HART / PROFIBUS PA / FOUNDATION Fieldbus)

---

**Frequency**

K-Band (~ 26 GHz)

---

**Antenna**

Parabolic DN200/8", DN250/10"  
Horn DN80/3", DN100/4"

---

**Accuracy**

+/- 15mm (or 0.04% of range, whatever is larger)

---

**Ambient temperature**

-40 °C...+80 °C  
(-40 °F...+176 °F)

---

**Process temperature**

-40 °C...+200 °C  
(-40 °F...+392 °F)

---

**Process pressure / max. overpressure limit**

Vacuum...16bar  
(Vaccum...232psi)

---

**Main wetted parts**

PEEK, 1.4435, 1.4404, 316L

---

---

**Continuous / Solids****Process connection**

Thread:

R1 1/2", NPT1 1/2

Flange:

DN80, DN 100

ASME 3", 4"

JIS 80A, 100A

UNI DN100/4"...DN250/10"

---

**Blocking distance**

Antenna length + 400mm (15.75")

---

**Max. measurement distance**

70 m (230 ft)

---

**Communication**

4...20 mA HART

PROFIBUS PA

FOUNDATION Fieldbus

---

**Certificates / Approvals**

ATEX, FM, CSA, NEPSI

SIL

---

**Options**

Separate display

Antenna extension 250 mm/ 10" or 450 mm/18"

Top Target Positioner (+/-15°)

---

**Application limits**

Dk &lt; 1.6

Reduction of the max. possible measuring range through:

Media with poor reflection properties

Angle of repose

Extremely loose surfaces of bulk solids, e.g. bulk solids with low bulk weight for pneumatic filling

Build-up, above all of moist products

More information [www.dk.endress.com/FMR250](http://www.dk.endress.com/FMR250)