

Field Xpert SFX350



More information and current pricing:

www.dk.endress.com/SFX350

Benefits:

- Simple device access, optimized device configuration, adaptable configuration templates and clear configuration reports save time during commissioning
- Explicit device documentation saves time during device exchange, transparent maintenance, diagnosis and trouble-shooting information increases the safety and availability of the plant
- High resolution full-VGA touchscreen (640x480 Pixel) makes operation simple
- High ingress protection and explosion protection allows Field Xpert to be used in all industries
- Seamless integration of calibration data into calibration management solutions saves time and increases the quality of device calibrations
- Mobile phone, camera (send as-is pictures immediately by email), 1D laser scanner (barcode), 2D imager (e.g. DataMatrix-Code, QR-Code) and RFID as standard or option increases labor productivity
- Open, vendor-independent operating system allows additional Asset Management applications to be run

Field of application: Field Xpert is an industrial PDA with integrated touchscreen for commissioning and maintaining field devices in explosion hazardous and safe areas*. It allows efficient configuration of FOUNDATION fieldbus, HART 5/6/7 and WirelessHART devices via Bluetooth and/or Wifi interfaces. From an application oriented view, Field Xpert is the mobile platform for Endress+Hauser Plant Asset Management applications. *Field Xpert SFX350 (safe areas) and Field Xpert SFX370 (explosion-hazardous areas).

Features and specifications

Fieldbus components

Measuring principle

Fieldbus components

Function

Ruggedized mobile computer (PDA) for commissioning and maintenance of field devices. Efficient device configuration and device diagnostics for HART and FOUNDATION fieldbus devices in Non-Ex-areas.

CPU

OMAP Multi Core Processor 1GHz

Memory

512 MB RAM, 1 GB Flash Memory,
16 GB Micro-SD Card (up to 32 GB supported)

Power supply

Lithium-ion battery, compliant with IEEE 1725 (removable, rechargeable), 3.7 Volts, 4000 mAh

Dimensions (WxHxD)

169 mm x 80 mm x 34 mm
(6.65" x 3.14" x 1.35")

Screen size

High resolution 3.5" touchscreen display, Gorilla glass protected, ambient light sensor, LED backlight, automatic portrait/landscape screen rotation.

Resolution

VGA (640 x 480 pixels), 65.536 colors

Communication interface

- USB
 - Wireless LAN
 - Bluetooth
 - Infrared
 - Wireless WAN (optional)
-

Operation

Operating system:
Microsoft Windows Embedded Handheld 6.5.3,
German or English (depending on the order)

Fieldbus components

Configuration

Configuration software:

- Device Xpert HART
- Device Xpert FOUNDATION fieldbus
- Device Xpert HART and Device Xpert FOUNDATION fieldbus

Optional

- Wireless WAN
- GPS

Certificates

Drop specification:

MIL-STD 810G

Electromagnetic Compatibility:

Interference conformance to

- EN 55022: 2006 + A1: 2007
- EN 61000-3-2: 2006
- EN 61000-3-3: 2008

Immunity conformance to

- EN 55024: 1998 + A1: 2001 + A2: 2002

Ingress protection:

IP67, NEMA Type 4

Explosion protection:

None

CE Mark

Hazardous area approval:

None

Telecommunication approval:

FCC w/HAC, Industries Canada, CE, A-tick (AU),
C-tick (NZ), NCC, OFTA, IDA, ICASA, POSTEL,
NTC, ETA, SIRIM, ANATEL, 61 countries in total

Electrical safety:

UL (DEMKO), cULus listed

More information www.dk.endress.com/SFX350