

Promag 10L



More information and current pricing:

www.endress.com/10L

Benefits:

- Reduced installation costs – flexible mounting by one-of-a-kind lap-joint flange concept (DN < 350/14")
- Energy-saving flow measurement – no pressure loss due to cross-section constriction
- Maintenance-free – no moving parts
- Cost-effective – designed for easy applications and direct integration
- Safe operation – display provides easily readable process information
- Fully industry compliant – IEC/EN/NAMUR

Specs at a glance

- **Max. measurement error** Volume flow: $\pm 0.5\%$ o.r. ± 2 mm/s ($\pm 0.5\%$ o.r. ± 0.08 in/s)
- **Measuring range** 9 dm³/min to 162 000 m³/h (2.5 gal/min to 1030 Mgal/d)
- **Medium temperature range** Liner material hard rubber: 0 to +80 °C (+32 to +176 °F) Liner material polyurethane: -20 to +50 °C (-4 to +122 °F) Liner material PTFE: -20 to +90 °C (-4 to +194 °F)
- **Max. process pressure** PN 16, Class 150
- **Wetted materials** Liner: PTFE; Polyurethane; Hard rubber
Electrodes: 1.4435 (316L); Alloy C22, 2.4602 (UNS N06022)

Field of application: Promag L is the versatile standard sensor for the water and wastewater industry with a lap-joint flange concept for flexible installation independent of the orientation of the pipe flange pitch diameter. Combined with the Promag 10 transmitter for basic applications and direct integration, Promag 10L offers accurate measurement of liquids for a wide range of applications. It will be the preferred solution for customers aiming for minimized cost of ownership.

Features and specifications

Liquids

Measuring principle

Electromagnetic

Product headline

std_productprofile_product_usp_8085.
std_productprofile_product_field_of_application_8025.

Sensor features

std_productprofile_product_benefits_8026. Energy-saving flow measure
pressure loss due to cross section constriction. Maintenance-free – no mo
std_productprofile_product_differentiating_tech_features_6649.
std_productprofile_product_differentiating_tech_features_6650.
std_successorproducts_product_differentiating_tech_features_35221_1

Transmitter features

std_productprofile_product_benefits_34707_1508943674.
std_productprofile_product_benefits_34705_1508943673.
std_productprofile_product_benefits_34706_1508943673.
2-line display with push buttons. Device as compact or remote version. H/

Nominal diameter range

Lap joint flange; lap joint flange, stamped plate: DN 25 to 300 (1 to 12")
Fixed flange: DN 350 to 2400 (14 to 90")

Wetted materials

Liner: PTFE; Polyurethane; Hard rubber
Electrodes: 1.4435 (316L); Alloy C22, 2.4602 (UNS N06022)

Measured variables

Volume flow

Max. measurement error

Volume flow: ± 0.5 % o.r. ± 2 mm/s (± 0.5 % o.r. ± 0.08 in/s)

Measuring range

9 dm³/min to 162 000 m³/h (2.5 gal/min to 1030 Mgal/d)

Max. process pressure

PN 16, Class 150

Liquids

Medium temperature range

Liner material hard rubber: 0 to +80 °C (+32 to +176 °F)

Liner material polyurethane: -20 to +50 °C (-4 to +122 °F)

Liner material PTFE: -20 to +90 °C (-4 to +194 °F)

Ambient temperature range

Flange material carbon steel: -10 to +60 °C (+14 to +140 °F)

Flange material stainless steel: -40 to +60 °C (-40 to +140 °F)

Sensor housing material

DN 25 to 300 (1 to 12"): AlSi10Mg, coated

DN 350 to 2400 (14 to 90"): Carbon steel with protective varnish

Sensor connection housing: AlSi10Mg, coated

Transmitter housing material

Powder-coated die-cast aluminum

Degree of protection

Compact version: IP66/67, type 4X enclosure

Sensor remote version (standard): IP66/67, type 4X enclosure

Sensor remote version (option): IP68, type 6P enclosure

Transmitter remote version: IP67, type 4X enclosure

Display/Operation

2-line display with push buttons

Configuration via local display and operating tools possible

Outputs

4-20 mA HART (active)

Pulse/switch output (passive)

Inputs

None

Digital communication

HART

Liquids

Power supply

DC 11 to 40 V

AC 85 to 250 V (45 to 65 Hz)

AC 20 to 28 V (45 to 65 Hz)

Hazardous area approvals

cCSAus

Product safety

CE, C-tick

Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 1

Hygienic approvals and certificates

Drinking water approval: ACS, KTW/W270, NSF 61, WRAS BS 6920

More information www.endress.com/10L