

Radar measurement Time-of-Flight Micropilot FMR52

For level measurement in aggressive liquids or applications with hygiene requirements



Lisätietoja ja ajankohtainen hinnasto:

www.fi.endress.com/FMR52

Edut:

- Hardware and software developed according to IEC 61508 up to SIL3 (in homogeneous redundancy)
- Reliable non-contact measurement even for changing product and process conditions
- HistoROM data management concept for fast and easy commissioning, maintenance and diagnostics
- Highest reliability even in the presence of obstructions in the vessel due to new Multi-Echo Tracking evaluation
- Heartbeat Technology for a cost-effective and safe plant operation during the entire life cycle
- Seamless integration into control or asset management systems and intuitive, menu-guided operation concept (on-site or via the control system)
- World's easiest proof test concept for SIL and WHG saves time and cost

Tärkeimmät tekniset tiedot

- **Accuracy** +/- 2 mm (0.08 in)
- **Process temperature** -196...+200 °C (-321...+392 °F)
- **Process pressure absolute / max. overpressure limit**
Vacuum...25 bar (Vacuum...363 psi)
- **Max. measurement distance** Standard: 40 m (131 ft) With advanced dynamics: 60 m (197 ft)
- **Main wetted parts** PTFE

Käyttöalue: For applications in aggressive liquids Micropilot FMR52 offers extraordinary advantages with its completely PTFE-filled and flush-mounted horn antenna. The FMR52 is also the sensor for hygiene-

sensitive applications in the food and life sciences industry - ASME BPE, USP Class VI, 3-A and EHEDG approvals. Micropilot is used for continuous, non-contact level measurement of liquids, pastes and slurries. The measurement is not affected by changing media, temperature changes, gas blankets or vapors.

Ominaisuudet ja tiedot

Continuous / Liquids

Mittausperiaate

Level radar

Characteristic / Application

Premium device for continuous non-contact level measurement, in which aggressive media are used as well as for highest hygiene requirements (ASME BPE, USP Class VI);

Flush mounted, fully PTFE filled horn antenna

Specialities

Heartbeat Technology,

SIL 2 according to IEC 61508,

Bluetooth® commissioning,

Operation and maintenance SmartBlue App,

Safety and reliability with Multi-Echo Tracking,

HistoROM,

RFID TAG for easy identification

Supply / Communication

2-wire (HART / PROFIBUS PA/ FOUNDATION Fieldbus)

4-wire (HART)

Bluetooth® wireless technology and App (optional)

Frequency

K-band (~26 GHz)

Accuracy

+/- 2 mm (0.08 in)

Continuous / Liquids

Ambient temperature

-50...+80 °C
(-58...+176 °F)

Process temperature

-196...+200 °C
(-321...+392 °F)

Process pressure absolute / max. overpressure limit

Vacuum...25 bar
(Vacuum...363 psi)

Main wetted parts

PTFE

Process connection

Flange:
DN50...DN150
ASME 2"...6"
JIS 10K

Process connection hygienic

Tri-Clamp ISO2852
DIN11851

Max. measurement distance

Standard: 40 m (131 ft)
With advanced dynamics: 60 m (197 ft)

Communication

4...20 mA HART
PROFIBUS PA
FOUNDATION Fieldbus
Bluetooth® wireless technology

Certificates / Approvals

ATEX, FM, CSA C/US, IEC Ex, JPN Ex, INMETRO, NEPSI, KC, EAC, UK Ex

Continuous / Liquids**Safety approvals**

Overfill protection WHG
SIL

Design approvals

EN 10204-3.1
ASME B31.3
AD2000

Hygienic approvals

3A, EHEDG
CoC ASME-BPE

Marine approval

GL/ ABS/ LR/ BV/ DNV

Options

Display,
Customized parameterization,
Remote operation via SmartBlue App using Bluetooth®,
Gas-tight feed through,
PWIS free

Application limits

Maximum measuring range is dependent on the tank form and/or application
Ammoniacal gas phase:
FMR54 in stilling well
Strong build-up formation:
FMR54 with air purge
Custody transfer measurement:
FMR5xx

Lisätietoja www.fi.endress.com/FMR52