

Proline Promag 51P electromagnetic flowmeter

The flowmeter for highest medium temperatures with a transmitter for custody transfer



Lisätietoja ja ajankohtainen hinnasto:

www.fi.endress.com/51P

Edut:

- Versatile applications – wide variety of wetted materials
- Energy-saving flow measurement – no pressure loss due to cross-section constriction
- Quality – designed for custody transfer; featuring worldwide recognized metrological approvals
- Safe operation – display provides easy readable process information
- Fully industry compliant – IEC/EN/NAMUR
- Maintenance-free – no moving parts

Tärkeimmät tekniset tiedot

- **Max. measurement error** $\pm 0.5\%$ $\pm 0.2\%$ (optional)
- **Measuring range** 0...9'600 m³/h
- **Medium temperature range** -40...+150°C (-40...+302°F)
- **Max. process pressure** PN10...40

Käyttöalue: Promag P is the preferred sensor for applications with highest requirements in a multitude of industries. Combined with the proven Promag 51 transmitter with push buttons, Promag 51P offers highly accurate measurement of liquids. Promag 51P is dedicated for chemical and process applications with corrosive liquids and high medium temperatures. It will be the preferred solution for customers needing custody transfer measurement. Promag 51P is available in a compact or remote version.

Ominaisuudet ja tiedot

Liquids

Mittausperiaate

Electromagnetic

Product headline

The flowmeter for highest medium temperatures with a transmitter for custody transfer. Dedicated for chemical and process applications with corrosive liquids and high medium temperatures.

Sensor features

Versatile applications – wide variety of wetted materials. Energy - saving flow measurement – no pressure loss due to cross - section constriction. Maintenance - free – no moving parts. Nominal diameter: max. DN 600 (24"). All common Ex approvals.

Transmitter features

Quality – designed for custody transfer; featuring worldwide recognized metrological approvals. Safe operation – display provides easy readable process information. Fully industry compliant – IEC/EN/NAMUR. Transmitter certified to MI - 001. Device in compact or remote version.

Nominal diameter range

DN 15...600

1/2"...24"

Max. measurement error

±0.5%

±0.2% (optional)

Measuring range

0...9'600 m³/h

Max. process pressure

PN10...40

Medium temperature range

-40...+150°C

(-40...+302°F)

Liquids

Ambient temperature range

-20...+60°C
-40...+60°C (optional)

Degree of protection

IP 67 (NEMA 4x)
IP 68 (Nema 6P)

Display/Operation

Two line display with backlit
Push button

Outputs

4...20 mA
Pulse/Frequency
Status

Inputs

Status

Digital communication

HART

Hazardous area approvals

ATEX

Product safety

CE, C-tick, EAC marking

Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)
Custody transfer approvals: MI-001, PTB

Lisätietoja www.fi.endress.com/51P