


iTHERM TMS01 MultiSens Flex Multipoint

Modular direct contact TC and RTD multipoint thermometer for oil, gas and petrochemical applications



Lisätietoja ja ajankohtainen hinnasto:

www.fi.endress.com/TMS01

Edut:

- Easy-to-use device with modular and flexible design, ready to be installed either for direct contact measurements or by means of sensor-dedicated protecting tubes. The device can also be installed in thermowells already in place
- Infinite layouts of 3D sensors distribution for any desired process monitoring configuration
- High degree of customization thanks to a modular product design for easy installation, process integration and maintenance
- High degree of insert process compatibility as per standard IEC 60584, ASTM E230 and IEC 60751
- On-board electronic heat protection for highest product durability
- Compliance to different types of protection for use in hazardous locations for easy process integration

Tärkeimmät tekniset tiedot

- **Accuracy** class 2 acc. to IEC 60584 ASTM E230 and ANSI MC 96.1
- **Response time** depending on configuration: TC: t50 = 2 s t90 = 5 s RTD: t50 = 0,8s t90 = 2s
- **Max. process pressure (static)** at 20 °C: 100 bar (1450 psi)
- **Operating temperature range** Type K: -270 °C ...1.100 °C (-454 °F ...2.012 °F) Type J: -210 °C ...760 °C (-346 °F ...1.382 °F) Type N: -270 °C ...1100 °C (-454 °F ...2.012 °F) Type T: -270 °C ...370 °C (-454 °F ...698 °F)
- **Max. immersion length on request** up to 30.000,00 mm (1181")

Käyttöalue: By complying with the highest safety standards, iTHERM TMS01 can be customized for various applications. Bendable into a 3D layout, it provides a complete temperature profile just by using one nozzle. The device is configurable with or without thermowells for optimal response times, mechanical strength or sensors replaceability. It is available either with TC or RTD technology or with our iTHERM StrongSens.

Ominaisuudet ja tiedot

Thermometer

Mittausperiaate

Resistance Temperature Detector

Characteristic / Application

metric style
 easy-to-use
 suitable for hazardous areas
 flanged process connection
 light chemical processes
 3D sensors distributions
 modular design
 replaceable sensors during shutdown

Thermowell / protection tube

without (for direct contact sensors type)
 with (for replaceable sensors)
 with (for increased mechanical protection)
 Multi-thermowells, each one dedicated to a sensor

Insert / probe

mineral insulated (MI), flexible
 mineral insulated (MI), flexible, with its own thermowell

Outer diameter protection tube / Insert

6,0 mm (0,24")
 8,0 mm (0,31")
 10,29 mm (1/8")

Thermometer**Max. immersion length on request**up to 30.000,00 mm (1181")

Material protection tube/ thermowell

1.4401 (316)

1.4435 (316L)

1.4541 (321)

1.4550 (347)

Alloy 600 (2.4816)

Process connection

flange:

2" ASME/ANSI B16.5 150

...600

3" ASME/ANSI B16.5 150

..600

4" ASME/ANSI B16.5 150

...600

6" ASME/ANSI B16.5 150

...600

8" ASME/ANSI B16.5 150

...600

DN80 EN/DIN 1092.1 PN10

...PN100

DN100 EN/DIN 1092.1 PN10

...PN100

DN125 EN/DIN 1092.1 PN10

...PN100

DN150 EN/DIN 1092.1 PN10

...PN100

DN200 EN/DIN 1092.1 PN10

...PN100

Tip shapestraight

Thermometer

Operating temperature range

Type K:

-270 °C ...1.100 °C

(-454 °F ...2.012 °F)

Type J:

-210 °C ...760 °C

(-346 °F ...1.382 °F)

Type N:

-270 °C ...1100 °C

(-454 °F ...2.012 °F)

Type T:

-270 °C ...370 °C

(-454 °F ...698 °F)

Max. process pressure (static)

at 20 °C: 100 bar (1450 psi)

Accuracy

class 2 acc. to IEC 60584

ASTM E230 and ANSI MC 96.1

Response time

depending on configuration:

TC:

t50 = 2 s

t90 = 5 s

RTD:

t50 = 0,8s

t90 = 2s

Integration head transmitter

yes (4 ... 20 mA; HART; PROFIBUS PA; FOUNDATION
FIELDBUS)

Ex - approvals

ATEX

IECEX

Thermometer

Certification

SIL (transmitter only)

Lisätietoja www.fi.endress.com/TMS01