

RLN22 isolating amplifier

Safe and reliable switching operations in critical systems



alk. **113,00 €**

Hinta 24.01.2022

Lisätietoja ja ajankohtainen hinnasto:

www.fi.endress.com/RLN22

Edut:

- Safe and reliable switching operations: trust your critical applications
- Compact housing: up to 2 channels on 12.5 mm (0.49 in) for efficient use of space in control cabinets
- Installation in hazardous areas; Ex approval for Ex zone 2
- Up to SIL 2 in accordance with IEC 61508
- Quick and easy wiring and commissioning: plug-in terminals, power supply and group error message module via DIN rail bus connector

Tärkeimmät tekniset tiedot

- **Input** NAMUR blocking: < 1,2 mA conducting: > 2,1 mA
- **Output** relay contact
- **Power Supply** 24 V DC

Käyttöalue: The RLN22 is a compact 1- or 2-channel, 24 V DC isolating amplifier with relay signal output. It is designed to safely operate e.g. proximity sensors or point level switches such as **Liquiphant FTL51B (NAMUR)** as per IEC 60947-5-6. The interface module monitors line faults such as breaks or short-circuits of sensors or mechanical switching contacts. The device is suited for use in hazardous areas and safety instrumented systems up to **SIL 2** in accordance with IEC 61508.

Ominaisuudet ja tiedot

Power supplies & barrier

Mittausperiaate

Active barrier

Measuring principle

NAMUR isolating amplifier

Power supplies & barrier

Function

1-channel, changeover contact
2-channel, normally open contact

Loop power supply

8 V DC

Power Supply

24 V DC

Auxiliary power supply / Loop power supply

8 V DC

Input

NAMUR
blocking: < 1,2 mA
conducting: > 2,1 mA

Output

relay contact

Certificates

ATEX
IECEX
DNV

SIL

SIL 2

Operation

DIP switch

Lisätietoja www.fi.endress.com/RLN22