

TR15

Modular RTD thermometer

Robust temperature measurement technology especially for gas and steam applications



Više informacija i trenutne cijene:

www.hr.endress.com/TR15

Prednosti:

- High degree of flexibility thanks to modular design with standard terminal heads as per DIN EN 50446 and customer-specific immersion lengths
- High degree of insert compatibility and design as per DIN 43772
- Extension neck to protect the head transmitter from overheating
- Fast response time with reduced/tapered tip form
- Types of protection for use in hazardous locations: Intrinsic safety (Ex i.a.), non-sparking (Ex nA)
- Head transmitter with easy selection: Analog output 4 to 20 mA, HART®, PROFIBUS® PA or FOUNDATION Fieldbus™

Kratke specifikacije

- **Accuracy** class A acc. to IEC 60751 class AA acc. to IEC 60751
- **Response time** depending on configuration
- **Max. process pressure (static)** at 20 °C: 400 bar (5.802 psi)
- **Operating temperature range** PT100 TF StrongSens: -50 °C ...500 °C (-58 °F ...932 °F) PT100 WW: -200 °C ...600 °C (-328 °F ...1.112 °F) PT100 TF: -50 °C ...400 °C (-58 °F ...752 °F)
- **Max. immersion length on request** up to 30.000,00 mm (1.181,10")

Područje primjene: The robust thermometer is designed for use in demanding applications like gas or steam applications e.g. in the Chemical, Oil & Gas and Energy industry. Highest pressures as well as high temperature can be handled by the use of robust protection tubes and special process connections. An optional head transmitter with all common communication protocols makes the device ready to use with

enhanced measurement accuracy and reliability compared to directly wired sensors.

Značajke i specifikacije

Thermometer

Mjerni princip

Resistance Temperature Detector

Characteristic / Application

metric style

modular temperature assembly

universal range of application

suitable for hazardous areas

suitable for high process pressures

flanged process connection or weld in

with neck

incl. thermowell (metal)

usable with insert StrongSens

Thermowell / protection tube

bar stock (drilled)

without thermowell

Insert / probe

mineral insulated (MI), flexible

Thermometer

Outer diameter protection tube / Insert

18,0 mm (0,71")

24,0 mm (0,94")

26,0 mm (1,02")

Max. immersion length on request

up to 30.000,00 mm (1.181,10")

Material protection tube/ thermowell

1.0460 (A105)

1.4571 (316Ti)

1.7335 (13CrMo4-5; F-11)

Alloy C276 (2.4819)

Duplex SAF 2205 (1.4462)

Titan Gr2 (3.7035)

16Mo3 (1.5415)

Optional coating

Not defined

Thermometer

Process connection

weld in version

flange:

DN25 PN40 B1 (EN1092)

DN40 PN40 B1(EN1092)

DN50 PN40 B1 (EN1092)

ASME 1" 150 RF (B16.5)

ASME 1" 300 RF (B16.5)

Tip shape

tapered

Surface roughness Ra0,8 μm (31,5 $\mu\text{in.}$)1,6 μm (63,0 $\mu\text{in.}$)

Thermometer**Operating temperature range**

PT100 TF StrongSens:

-50 °C ...500 °C

(-58 °F ...932 °F)

PT100 WW:

-200 °C ...600 °C

(-328 °F ...1.112 °F)

PT100 TF:

-50 °C ...400 °C

(-58 °F ...752 °F)

Max. process pressure (static)

at 20 °C: 400 bar (5.802 psi)

Accuracy

class A acc. to IEC 60751

class AA acc. to IEC 60751

Response time

depending on configuration

Integration head transmitteryes (4 ... 20 mA; HART; PROFIBUS PA; FOUNDATION
FIELDBUS)

Thermometer

Ex - approvals

ATEX II

NEPSI

IECEX

EAC Ex

Certification

Gost Metrology

SIL (transmitter only)

Više informacija www.hr.endress.com/TR15