

RIA16

Loop-powered indicator

Excellent readable indication of 4...20 mA signal with trend bar graph for a better process overview



Benefits:

- Display of 4 to 20 mA measured values
- 5-digit measured value display with dimension, bar graph and backlight
- No external power supply required
- Versions: Fiber glass reinforced plastic respectively aluminum for Ex-applications
- Easy 3-key operation; or configuration with FieldCare PC software; or configuration without power supply using setup box
- International approvals; marine approval
- Allows the HART® transmission protocol to pass unimpeded

Specs at a glance

- **Input** 1 x analogue 4...20 mA
- **Output** 1 x open collector
- **Output** 1 x open collector
- **Display** LCD 26 mm (1.02") 5-digit Bargraph Plain text display
- **Power Supply** Loop powered

from **€211.00**

Price as of 22.09.2021

More information and current pricing:

www.ie.endress.com/RIA16

Field of application: The indicator shows the measured signal on the large, backlit display. A bar graph indicates the value graphically for a quick process overview. An editable plain text field displays further information like engineering unit or TAG. Limit value infringement is also signaled and an open collector can be switched. The indicator is powered directly from the 4...20 mA loop and doesn't need a separate power supply. For applications in hazardous areas the device is available with Ex approvals.

Features and specifications

Acquisition / Evaluation

Measuring principleDisplay

FunctionDisplay

Certification

UR C/US

CSA GP

ATEX Ex i

FM USA NI

FM USA DIP

CSA NI

CSA DIP

Marine approval

Input1 x analogue 4...20 mA

Output1 x open collector

Auxiliary power supply / Loop power supplyLoop powered

Acquisition / Evaluation

Dimensions (wxhxd)

Field housing:

199 x 133 x 96 mm

(7.83" x 5.24" x 3.78")

Operation

3 keys interface on electronics + PC interface

FieldCare

Display

LCD 26 mm (1.02")

5-digit

Bargraph

Plain text display

Process indicator & control units

Measuring principle

Loop powered indicators

Measuring principle

Loop-powered field indicator

Function

Display

Process indicator & control units**Display**

LCD 26 mm (1.02")

5-digit

Bargraph

Plain text display

Power SupplyLoop powered

Input1 x analogue 4...20 mA

Output1 x open collector

Output1 x open collector

Software functionsNot defined

Process indicator & control
units

Certificates

UR C/US

CSA GP

ATEX Ex i

FM USA NI

FM USA DIP

CSA NI

CSA DIP

EAC

Marine approval

SIL

Not defined

Panel mounting

field

More information www.ie.endress.com/RIA16