


## System power supply RNB130



More information and current pricing:

[www.jp.endress.com/RNB130](http://www.jp.endress.com/RNB130)

### Benefits:

- Small housing, 35 mm width
- High availability
- Wide range input - can be used world-wide
- Power reserve (Power Boost)
- Power supply without wiring: Supply via DIN rail bus connector
- Space saving DIN rail mounting as per IEC 60715

### Specs at a glance

- **Output** 24 VDC, 1,5 A
- **Power Supply** 100...240 V AC (wide range power supply) 45...65 Hz

**Field of application:** The power supply has one output for supplying voltage to 4 wire sensors and transmitters. Connection to mono-phased a.c. networks or to two phase conductors of three-phase supply networks (TN-, TT- or IT-networks as per VDE 0100 T 300/IEC 364-3) with 100-240 V AC nominal voltage possible.

## Features and specifications

### Power supplies & barrier

#### Measuring principle

Power supply

#### Measuring principle

Power supply

#### Function

Power supply for one 4-wire sensor or transmitter

## Power supplies &amp; barrier

**Loop power supply**

24 V DC

**Power Supply**

100...240 V AC (wide range power supply)

45...65 Hz

**Auxiliary power supply / Loop power supply**

85...250 V AC

45...65 Hz

**Output**

24 VDC, 1,5 A

**Operation**

DIP switch

## Acquisition / Evaluation

**Measuring principle**

Power supply

**Function**

Power

**Output**

24 VDC, 1,5 A

**Auxiliary power supply / Loop power supply**

85...250 V AC

45...65 Hz

**Dimensions (wxhxd)**

35 x 99 x 102.5 mm

(1.39" x 3.9" x 4.04")

**Operation**

DIP switch

More information [www.jp.endress.com/RNB130](http://www.jp.endress.com/RNB130)