

Proline Promass Q 300 Coriolis flowmeter

Innovative specialist for challenging applications with a compact, easily accessible transmitter



More information and current pricing:

www.si.endress.com/8Q3B

Benefits:

- Secured measuring quality – unmatched accuracy of mass flow, volume flow and density
- Optimized performance for liquids with entrained gas – MFT (Multi-Frequency Technology)
- Fewer process measuring points – multivariable measurement (flow, density, temperature)
- Space-saving installation – no in/outlet run needs
- Full access to process and diagnostic information – numerous, freely combinable I/Os and fieldbuses
- Reduced complexity and variety – freely configurable I/O functionality
- Integrated verification – Heartbeat Technology

Specs at a glance

- **Max. measurement error** Mass flow (liquid): $\pm 0.10\%$ (standard), 0.05% (option) Volume flow (liquid): $\pm 0.10\%$ Mass flow (gas): $\pm 0.35\%$ Density (liquid): $\pm 0.2\text{ kg/m}^3$
- **Measuring range** 0 to 550 000 kg/h (0 to 20 210 lb/min)
- **Medium temperature range** Standard: -50 to $+205^\circ\text{C}$ (-58 to $+401^\circ\text{F}$) Option: -196 to $+150^\circ\text{C}$ (-321 to $+302^\circ\text{F}$)
- **Max. process pressure** PN 100, Class 600, 63K
- **Wetted materials** Measuring tube: 1.4404 (316/316L); stainless steel for cryogenic applications Connection: 1.4404 (316/316L)

Field of application: Promass Q 300 provides the highest measurement accuracy for mass flow, volume flow and density. Being the preferred choice for custody transfer applications, it has also been optimized for liquid applications where entrained gas is known to be present. The

compact transmitter offers high flexibility in terms of operation and system integration: access from one side, remote display and improved connectivity options. Heartbeat Technology ensures compliance and process safety at all times.

Features and specifications

Steam

Measuring principle

Coriolis

Product headline

Innovative specialist for challenging applications with a compact, easily accessible transmitter. Secured measuring quality – unmatched accuracy of mass flow, volume flow and density. Highest measurement performance for custody transfer, density and tough process conditions.

Marine approvals and certificates

LR approval, DNV GL approval, ABS approval, BV approval

Liquids

Measuring principle

Coriolis

Product headline

Innovative specialist for challenging applications with a compact, easily accessible transmitter. Secured measuring quality – unmatched accuracy of mass flow, volume flow and density. Highest measurement performance for custody transfer, density and tough process conditions.

Sensor features

Optimized performance for liquids with entrained gas – MFT (Multi-Frequency Technology). Fewer process measuring points – multivariable measurement (flow, density, temperature). Space-saving installation – no in/outlet run needs. Mass flow: measurement error $\pm 0.05\%$ (PremiumCal). Density: measurement error $\pm 0.2 \text{ kg/m}^3$.

Liquids

Transmitter features

Full access to process and diagnostic information – numerous, freely combinable I/Os and fieldbuses. Reduced complexity and variety – freely configurable I/O functionality. Integrated verification – Heartbeat Technology. Compact dual-compartment housing with up to 3 I/Os. Backlit display with touch control and WLAN access.

Nominal diameter range

DN 25 to 100 (1 to 4")

Wetted materials

Measuring tube: 1.4404 (316/316L); stainless steel for cryogenic applications

Connection: 1.4404 (316/316L)

Measured variables

Mass flow, density, temperature, volume flow, corrected volume flow, reference density, concentration

Max. measurement error

Mass flow (liquid): ± 0.10 % (standard), 0.05 % (option)

Volume flow (liquid): ± 0.10 %

Mass flow (gas): ± 0.35 %

Density (liquid): ± 0.2 kg/m³

Measuring range

0 to 550 000 kg/h (0 to 20 210 lb/min)

Max. process pressure

PN 100, Class 600, 63K

Medium temperature range

Standard: -50 to $+205$ °C (-58 to $+401$ °F)

Option: -196 to $+150$ °C (-321 to $+302$ °F)

Ambient temperature range

Standard: -40 to $+60$ °C (-40 to $+140$ °F)

Option: -50 to $+60$ °C (-58 to $+140$ °F)

Liquids

Sensor housing material

1.4404 (316L), highest corrosion resistance

Transmitter housing material

AlSi10Mg, coated; 1.4409 (CF3M) similar to 316L; stainless steel for hygienic transmitter design

Degree of protection

IP66/67, type 4X enclosure

IP69

Display/Operation

4-line backlit display with touch control (operation from outside)

Configuration via local display and operating tools possible

Remote display available

Outputs

3 outputs:

4-20 mA HART (active/passive)

4-20 mA WirelessHART

4-20 mA (active/passive)

Pulse/frequency/switch output (active/passive)

Double pulse output (active/passive)

Relay output

Inputs

Status input

4-20 mA input

Digital communication

HART, PROFIBUS DP, PROFIBUS PA, FOUNDATION Fieldbus, Modbus RS485, Profinet, Ethernet/IP, OPC-UA

Power supply

DC 24 V

AC 100 to 230 V

AC 100 to 230 V / DC 24 V (non-hazardous area)

Liquids

Hazardous area approvals

ATEX, IECEx, cCSAus, NEPSI, INMETRO, EAC

Product safety

CE, C-tick, EAC marking

Functional safety

Functional safety according to IEC 61508, applicable in safety-relevant applications in accordance with IEC 61511

Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

MI-005 Liquids other than water (Hydrocarbons, Liquified gases, Cryogenic liquids)

OIML R117 (Liquids other than water, Liquified gases, Cryogenic liquids)

NTEP (Liquids other than water, Cryogenic liquids)

MC (Liquids other than water, Cryogenic liquids)

Marine approvals and certificates

LR approval, DNV GL approval, ABS approval, BV approval

Pressure approvals and certificates

PED, CRN, AD 2000

Material certificates

3.1 material

NACE MR0175/MR0103, PMI; welding test acc. to EN ISO, ASME, NORSOK

Hygienic approvals and certificates

3-A, EHEDG, cGMP

Density

Measuring principle

Coriolis

Product Headline

Innovative specialist for challenging applications with a compact, easily accessible transmitter. Secured measuring quality – unmatched accuracy of mass flow, volume flow and density. Highest measurement performance for custody transfer, density and tough process conditions.

Sensor features

Optimized performance for liquids with entrained gas – MFT (Multi-Frequency Technology). Fewer process measuring points – multivariable measurement (flow, density, temperature). Space-saving installation – no in/outlet run needs. Mass flow: measurement error $\pm 0.05\%$ (PremiumCal). Density: measurement error $\pm 0.2 \text{ kg/m}^3$.

Transmitter features

Full access to process and diagnostic information – numerous, freely combinable I/Os and fieldbuses. Reduced complexity and variety – freely configurable I/O functionality. Integrated verification – Heartbeat Technology. Compact dual-compartment housing with up to 3 I/Os. Backlit display with touch control and WLAN access.

Nominal diameter range

DN 25 to 100 (1 to 4")

Wetted materials

Measuring tube: 1.4404 (316/316L); stainless steel for cryogenic applications

Connection: 1.4404 (316/316L)

Measured variables

Mass flow, density, temperature, volume flow, corrected volume flow, reference density, concentration

Density

Max. measurement error

Mass flow (liquid): $\pm 0.10\%$ (standard), 0.05% (option)

Volume flow (liquid): $\pm 0.10\%$

Mass flow (gas): $\pm 0.35\%$

Density (liquid): $\pm 0.2\text{ kg/m}^3$

Measuring range

0 to 550 000 kg/h (0 to 20 210 lb/min)

Max. process pressure

PN 100, Class 600, 63K

Medium temperature range

Standard: -50 to $+205^\circ\text{C}$ (-58 to $+401^\circ\text{F}$)

Option: -196 to $+150^\circ\text{C}$ (-321 to $+302^\circ\text{F}$)

Ambient temperature range

Standard: -40 to $+60^\circ\text{C}$ (-40 to $+140^\circ\text{F}$)

Option: -50 to $+60^\circ\text{C}$ (-58 to $+140^\circ\text{F}$)

Sensor housing material

1.4404 (316L), highest corrosion resistance

Transmitter housing material

AlSi10Mg, coated; 1.4409 (CF3M) similar to 316L; stainless steel for hygienic transmitter design

Degree of protection

IP66/67, type 4X enclosure

IP69

Display/Operation

4-line backlit display with touch control (operation from outside)

Configuration via local display and operating tools possible

Remote display available

Density**Outputs**

3 outputs:

4-20 mA HART (active/passive)

4-20 mA WirelessHART

4-20 mA (active/passive)

Pulse/frequency/switch output (active/passive)

Double pulse output (active/passive)

Relay output

Inputs

Status input

4-20 mA input

Digital communication

HART, PROFIBUS DP, PROFIBUS PA, FOUNDATION Fieldbus, Modbus RS485, Profinet, Ethernet/IP, OPC-UA

Power supply

DC 24 V

AC 100 to 230 V

AC 100 to 230 V / DC 24 V (non-hazardous area)

Hazardous area approvals

ATEX, IECEx, cCSAus, NEPSI, INMETRO, EAC

Density**Other approvals and certificates**

CE, C-tick, EAC marking

Functional safety according to IEC 61508, applicable in safety-relevant applications in accordance with IEC 61511

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

MI-005 Liquids other than water (Hydrocarbons, Liquified gases, Cryogenic liquids)

OIML R117 (Liquids other than water, Liquified gases, Cryogenic liquids)

NTEP (Liquids other than water, Cryogenic liquids)

MC (Liquids other than water, Cryogenic liquids)

LR approval, DNV GL approval, ABS approval, BV approval

PED, CRN, AD 2000

3.1 material

NACE MR0175/MR0103, PMI; welding test acc. to EN ISO, ASME, NORSOK

3-A, EHEDG, cGMP

Density/Concentration**Measuring principle**

Coriolis

Density/Concentration

Product headline

Innovative specialist for challenging applications with a compact, easily accessible transmitter. Secured measuring quality – unmatched accuracy of mass flow, volume flow and density. Highest measurement performance for custody transfer, density and tough process conditions.

Sensor features

Optimized performance for liquids with entrained gas – MFT (Multi-Frequency Technology). Fewer process measuring points – multivariable measurement (flow, density, temperature). Space-saving installation – no in/outlet run needs. Mass flow: measurement error ± 0.05 % (PremiumCal). Density: measurement error ± 0.2 kg/m³.

Transmitter features

Full access to process and diagnostic information – numerous, freely combinable I/Os and fieldbuses. Reduced complexity and variety – freely configurable I/O functionality. Integrated verification – Heartbeat Technology. Compact dual-compartment housing with up to 3 I/Os. Backlit display with touch control and WLAN access.

Nominal diameter range

DN 25 to 100 (1 to 4")

Wetted materials

Measuring tube: 1.4404 (316/316L); stainless steel for cryogenic applications

Connection: 1.4404 (316/316L)

Measured variables

Mass flow, density, temperature, volume flow, corrected volume flow, reference density, concentration

Max. measurement error

Mass flow (liquid): ± 0.10 % (standard), 0.05 % (option)

Volume flow (liquid): ± 0.10 %

Mass flow (gas): ± 0.35 %

Density (liquid): ± 0.2 kg/m³

Density/Concentration**Measuring range**

0 to 550 000 kg/h (0 to 20 210 lb/min)

Max. process pressure

PN 100, Class 600, 63K

Medium temperature range

Standard: -50 to +205°C (-58 to +401 °F)

Option: -196 to +150 °C (-321 to +302 °F)

Ambient temperature range

Standard: - 40 to +60 °C (-40 to +140 °F)

Option: -50 to +60 °C (-58 to +140 °F)

Sensor housing material

1.4404 (316L), highest corrosion resistance

Transmitter housing material

AlSi10Mg, coated; 1.4409 (CF3M) similar to 316L; stainless steel for hygienic transmitter design

Degree of protection

IP66/67, type 4X enclosure

IP69

Display/Operation

4-line backlit display with touch control (operation from outside)

Configuration via local display and operating tools possible

Remote display available

Outputs

3 outputs:

4-20 mA HART (active/passive)

4-20 mA WirelessHART

4-20 mA (active/passive)

Pulse/frequency/switch output (active/passive)

Double pulse output (active/passive)

Relay output

Density/Concentration**Inputs**

Status input
4-20 mA input

Digital communication

HART, PROFIBUS DP, PROFIBUS PA, FOUNDATION Fieldbus, Modbus
RS485, Profinet, Ethernet/IP, OPC-UA

Power supply

DC 24 V
AC 100 to 230 V
AC 100 to 230 V / DC 24 V (non-hazardous area)

Hazardous area approvals

ATEX, IECEx, cCSAus, NEPSI, INMETRO, EAC

Product safety

CE, C-tick, EAC marking

Functional safety

Functional safety according to IEC 61508, applicable in safety-relevant applications in accordance with IEC 61511

Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)
Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)
MI-005 Liquids other than water (Hydrocarbons, Liquified gases, Cryogenic liquids)
OIML R117 (Liquids other than water, Liquified gases, Cryogenic liquids)
NTEP (Liquids other than water, Cryogenic liquids)

Marine approvals and certificates

LR approval, DNV GL approval, ABS approval, BV approval

Pressure approvals and certificates

PED, CRN, AD 2000

Density/Concentration

Material certificates

3.1 material

NACE MR0175/MR0103, PMI; welding test acc. to EN ISO, ASME, NORSOK

Hygienic approvals and certificates

3-A, EHEDG, cGMP

Gas

Measuring principle

Coriolis

Product headline

Innovative specialist for challenging applications with a compact, easily accessible transmitter. Secured measuring quality – unmatched accuracy of mass flow, volume flow and density. Highest measurement performance for custody transfer, density and tough process conditions.

Sensor features

Optimized performance for liquids with entrained gas – MFT (Multi-Frequency Technology). Fewer process measuring points – multivariable measurement (flow, density, temperature). Space-saving installation – no in/outlet run needs. Mass flow: measurement error $\pm 0.05\%$ (PremiumCal). Density: measurement error $\pm 0.2 \text{ kg/m}^3$.

Transmitter features

Full access to process and diagnostic information – numerous, freely combinable I/Os and fieldbuses. Reduced complexity and variety – freely configurable I/O functionality. Integrated verification – Heartbeat Technology. Compact dual-compartment housing with up to 3 I/Os. Backlit display with touch control and WLAN access.

Nominal diameter range

DN 25 to 100 (1 to 4")

Gas

Wetted materials

Measuring tube: 1.4404 (316/316L); stainless steel for cryogenic applications

Connection: 1.4404 (316/316L)

Measured variables

Mass flow, density, temperature, volume flow, corrected volume flow, reference density, concentration

Max. measurement error

Mass flow (liquid): ± 0.10 % (standard), 0.05 % (option)

Volume flow (liquid): ± 0.10 %

Mass flow (gas): ± 0.35 %

Density (liquid): ± 0.2 kg/m³

Measuring range

0 to 400 000 kg/h (0 to 14 697 lb/min)

Max. process pressure

PN 100, Class 600, 63K

Medium temperature range

Standard: -50 to $+205$ °C (-58 to $+401$ °F)

Option: -196 to $+150$ °C (-321 to $+302$ °F)

Ambient temperature range

Standard: -40 to $+60$ °C (-40 to $+140$ °F)

Option: -50 to $+60$ °C (-58 to $+140$ °F)

Sensor housing material

1.4404 (316L), highest corrosion resistance

Transmitter housing material

AlSi10Mg, coated; 1.4409 (CF3M) similar to 316L; stainless steel for hygienic transmitter design

Degree of protection

IP66/67, type 4X enclosure

IP69

Gas

Display/Operation

4-line backlit display with touch control (operation from outside)
Configuration via local display and operating tools possible
Remote display available

Outputs

3 outputs:
4-20 mA HART (active/passive)
4-20 mA WirelessHART
4-20 mA (active/passive)
Pulse/frequency/switch output (active/passive)
Double pulse output (active/passive)
Relay output

Inputs

Status input
4-20 mA input

Digital communication

HART, PROFIBUS DP, PROFIBUS PA, FOUNDATION Fieldbus, Modbus
RS485, Profinet, Ethernet/IP, OPC-UA

Power supply

DC 24 V
AC 100 to 230 V
AC 100 to 230 V / DC 24 V (non-hazardous area)

Hazardous area approvals

ATEX, IECEx, cCSAus, NEPSI, INMETRO, EAC

Product safety

CE, C-tick, EAC marking

Functional safety

Functional safety according to IEC 61508, applicable in safety-relevant applications in accordance with IEC 61511

Gas

Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

MI-005 Liquids other than water (Hydrocarbons, Liquified gases, Cryogenic liquids)

OIML R117 (Liquids other than water, Liquified gases, Cryogenic liquids)

NTEP (Liquids other than water, Cryogenic liquids)

Marine approvals and certificates

LR approval, DNV GL approval, ABS approval, BV approval

Pressure approvals and certificates

PED, CRN, AD 2000

Material certificates

3.1 material

NACE MR0175/MR0103, PMI; welding test acc. to EN ISO, ASME, NORSOK

Hygienic approvals and certificates

3-A, EHEDG, cGMP

More information www.si.endress.com/8Q3B