

Liquiphant FTL62 - the specialist for aggressive media

A level switch for aggressive and pumpable liquids



Prednosti:

- Universal measuring principle for limit detection – proven vibronic technology
- Developed according IEC 61508 for highest safety – SIL2/3 applications (3rd party approved)
- Periodic proof testing is quickly and simple organized with guided wizards via the SmartBlue-App or via a test button or magnetic pin from outside. Via digital communication you can initiate the device for a fast and easy testing of the safety loop.
- **Heartbeat Technology** allows safe, continuous diagnostics and a simple verification, without process interruption
- Centralized asset management with easy online access to all device information thanks to digital communication
- Second line of defense to protect the environment

Več informacij in aktualne cene:

www.si.endress.com/FTL62

Lastnosti na dlani

- **Process temperature** -50 °C...+150 °C (-58 °F...+302 °F)
- **Process pressure / max. overpressure limit** Vacuum...40 bar
Vacuum...580 psi
- **Min. density of medium** 0.5 g/cm³ (0.4 g/cm³ optional)

Področje uporabe: Liquiphant FTL62 has a strong focus on specific applications with aggressive liquids and simplicity with easy proof testing, reliability and safety (SIL) with compliance to IEC 61508, API 2350 and WHG. The vibronic device is determined for a safe and active measuring technology in aggressive liquids and want a reliable and proven point level detection for tank overfill prevention and pump dry run protection. The FTL62 is easy to use, has a digital connection and gives a real-time data at hand.

Lastnosti in specifikacije

Point Level / Liquids

Merilni princip

Vibration Liquids

Characteristic / Application

Compact vibronic device with highly corrosion-resistant coating for aggressive media,
Optional extension tube up to 3 m (9.8ft),
Modular housing concept

Specialities

Heartbeat Technology,
Bluetooth® Operation and maintenance SmartBlue App,
LED Module,
RFID TAG for easy identification,
Second line of defense
Temperature spacer for high process temperature,
Plug and play functionalities

Supply / Communication

19...253V AC / 2-wire,
10...55V / DC-PNP 3-wire,
9...20V DC with relay DPDT,
19...253V AC or 19...55V DC with relay DPDT,
2-wire NAMUR,
2-wire PFM,
4-20mA HART

Ambient temperature

-60 °C...+70 °C
(-76 °F...+158 °F)

Process temperature

-50 °C...+150 °C
(-58 °F...+302 °F)

Point Level / Liquids**Process pressure / max. overpressure limit**

Vacuum...40 bar

Vacuum...580 psi

Min. density of medium0.5 g/cm³(0.4 g/cm³ optional)

Main wetted parts

ECTFE,

PFA (Edlon, RubyRed or conductive)

316L

Enamel

Process connection

Flanges:

DN25...DN100

ASME 1"...4"

JIS 50A

Sensor length

Up to 3 m (9.8 ft)

Communication

2-wire direct load

HART

DC-PNP 3-wire

Relays

NAMUR

PFM

Bluetooth® wireless technology

Certificates / Approvals

ATEX, IEC Ex, NEPSI, EAC Ex

Safety approvals

Overfill protection WHG

SIL2/ SIL 3 according to IEC 61508

Point Level / Liquids**Design approvals**

EN 10204-3.1
ASME B31.3 Process Piping
CRN

Marine approval

ABS/ LR/ BV/ DNV GL

Options

Ambient temperature down to -60 °C (-76 °F),
Heavy duty stainless steel housing

Components

FTL325P Interface PFM
FTL325N Interface NAMUR

Density**Merilni princip**

Vibration Density

Product Headline

Coated Liquiphant with Density Computer FML621

Characteristic / Application

Compact vibronic device with highly corrosion-resistant coating for aggressive media,
Optional extension tube up to 3 m (9.8ft),
Modular housing concept

Ambient temperature

-60 °C...+70 °C
(-51 °F...+158 °F)

Process temperature

-50 °C...+150 °C
(-58 °F...+302 °F)

Density

Process pressure

Vacuum...40 bar

Vacuum...580 psi

Sensor length

Up to 3 m (9.8ft)

Certificates / Approvals

ATEX, IEC Ex

Specialities

Heartbeat Technology,
Bluetooth® Operation and maintenance SmartBlue App,
LED Module,
RFID TAG for easy identification,
Second line of defense
Temperature spacer for high process temperature,
Plug and play functionalities

Components

Density Computer FML621

Measuring range

Density range: 0.3 to 2 g/cm³

Other approvals and certificates

Overfill protection WHG

SIL2/ SIL 3 according to IEC 61508

Več informacij www.si.endress.com/FTL62