

# Ultrasonic measurement Time-of-Flight Prosonic FDU91

Ultrasonic sensor for level and flow measurement for connection to FMU9x (measuring range up to 10m)



## Prednosti:

- Integrated temperature sensor for Time-of-Flight correction. Accurate measurements are possible, even if temperature changes are present
- Hermetically welded PVDF sensor for highest chemical resistance
- Suited for rough ambient conditions thanks to separate installation from the transmitter (up to 300m)
- Reduced build-up formation because of the self-cleaning effect
- Integrated automatic sensor detection for transmitters FMU90/ FMU95 for simple commissioning
- Weather resistant and flood-proof (IP 68)
- Integrated heating against a build-up of ice at the sensor (optional) ensures reliable measurement

Več informacij in aktualne cene:

[www.si.endress.com/FDU91](http://www.si.endress.com/FDU91)

## Lastnosti na dlani

- **Process temperature** -40 °C ... 80 °C (-40 °F ... 176 °F)
- **Process pressure / max. overpressure limit** 0.7 bar ... 4 bar abs (10 psi ... 58 psi)
- **Max. measurement distance** Liquids: 10 m (33 ft), Solids: 5 m (16 ft)
- **Accuracy** +/- 2mm + 0.17% of measured distance
- **Main wetted parts** PVDF (fully welded IP68 / NEMA 6P)

**Področje uporabe:** The FDU91 ultrasonic sensor for continuous, non-contact and maintenance-free level measurement of fluids, pastes, sludges and powdery to coarse bulk materials. But also for flow measurement in open channels and measuring weirs. The measurement

is unaffected by dielectric constant, density or humidity and also unaffected by build-up due to the self-cleaning effect of sensors. Suited for explosion hazardous areas. Maximum measuring range in liquids 10m (33ft), solids 5m (16ft).

## Lastnosti in specifikacije

### Continuous / Liquids

**Merilni princip**

Ultrasonic

**Characteristic / Application**

Separated version with field housing or top hat rail housing for control cabinet instrumentation, 300 m in-between sensor and transmitter

**Supply / Communication**

4-wire (HART, Profibus DP)

**Accuracy**

+/- 2 mm + 0.17% of measured distance

**Ambient temperature**

-40 °C ... 80 °C  
(-40 °F ... 176 °F)

**Process temperature**

-40 °C ... 80 °C  
(-40 °F ... 176 °F)

**Process pressure / max. overpressure limit**

0.7 bar ... 4 bar abs  
(10 psi ... 58 psi)

**Main wetted parts**

PVDF (fully welded IP68 / NEMA6P)

**Process connection**

G / NPT 1"

---

**Continuous / Liquids****Blocking distance**0.3 m (1 ft)

---

**Max. measurement distance**

Liquids: 10 m (33 ft),

Solids: 5 m (16 ft)

---

**Communication**

Transmitter:

4 ... 20 mA HART

Profibus DP

---

**Certificates / Approvals**ATEX, FM, CSA, IEC Ex, INMETRO, NEPSI, EAC Ex

---

**Options**Second 4...20 mA output

---

**Components**

Transmitter:

FMU90, FMU95

---

**Application limits**

Foam / high turbulence possible:

FDU92

Flange-flush assembly:

FDU91F

For tank farms scanner:

FMU95

---

**Continuous / Solids****Merilni princip**Ultrasonic

---

**Characteristic / Application**Separated version with field housing or top hat rail housing for control cabinet instrumentation, 300m in-between sensor and transmitter

---

---

**Continuous / Solids****Supply / Communication**4-wire (HART , Profibus DP)

---

**Accuracy**+/- 2mm + 0.17% of measured distance

---

**Ambient temperature**-40 °C ... 80 °C  
(-40 °F ... 176 °F)

---

**Process temperature**-40 °C ... 80 °C  
(-40 °F ... 176 °F)

---

**Process pressure / max. overpressure limit**0.7 bar ... 4 bar abs  
(10 psi ... 58 psi)

---

**Main wetted parts**PVDF (fully welded IP68 / NEMA 6P)

---

**Process connection**G / NPT 1"

---

**Blocking distance**0.3 m (1 ft)

---

**Max. measurement distance**Liquids: 10 m (33 ft),  
Solids: 5 m (16 ft)

---

**Communication**Transmitter:  
4 ... 20 mA HART  
Profibus DP

---

**Certificates / Approvals**ATEX, FM, CSA, IEC Ex, JPN Ex, INMETRO, NEPSI, EAC Ex

---

---

**Continuous / Solids****Options**

Second 4...20mA output

---

**Components**

Transmitter:  
FMU90

---

**Liquids****Merilni princip**

Ultrasonic

---

**Product headline**

Version with separate transmitter in field housing or top hat rail housing  
Cost effective solution for open channel flow measurement in water /  
wastewater plants

---

**Max. measurement error**

accuracy:

distance measurement: +/- 2mm + 0.17%

resolution:

distance measurement: 1mm

---

**Measuring range**

max measuring distance up to 10m / 32ft

---

**Max. process pressure**

atm.

---

**Medium temperature range**

-40...80°C

(-40...176°F)

---

**Degree of protection**

IP68

---

**Display/Operation**

Transmitter

---

## Liquids

### Outputs

Transmitter:

4...20mA HART

Option: second 4...20mA output

---

### Inputs

Transmitter

---

### Digital communication

HART, PROFIBUS DP

---

### Hazardous area approvals

ATEX, FM, CSA, IEC Ex, INMETRO, NEPSI, EAC Ex

---

Več informacij [www.si.endress.com/FDU91](http://www.si.endress.com/FDU91)