

Ammonium analyzer Liquiline System CA80AM

Colorimetric system for online monitoring of water and wastewater treatment



Več informacij in aktualne cene:

www.si.endress.com/CA80AM

Prednosti:

- Fast commissioning and plug & play thanks to Memosens technology and user-friendly operation
- Easy upgrade of functionality - even to a complete measuring station - simply by adding modules and connecting Memosens sensors
- Advanced diagnostics with remote access for increased process safety
- Reduced operating costs through automatic, configurable calibration and cleaning and long reagent shelf life with optional cooling module
- Compliance with standard colorimetric measuring principle - indophenol blue method - following ISO 7150-1, DIN 38406-5 and GB 7481-87

Lastnosti na dlani

- **Measurement range** 0.05 to 20 mg/l NH₄-N 0.5 to 50 mg/l NH₄-N 1 to 100 mg/l NH₄-N 0.5 to 50 mg/l with dilution function to maximum 10 to 1000 mg/l NH₄-N
- **Process temperature** 4 to 40 °C (39 to 104 °F)
- **Process pressure** Unpressurized
- **Measuring method** Comply with standard colorimetric measuring principle - indophenol blue method following ISO 7150-1, DIN 38406-5 and GB 7481-87

Področje uporabe: Liquiline System CA80AM offers high-precision ammonium measurement in all critical control points. As member of the Liquiline platform, it enables plug & play and easy upgrade to a measuring station - minimizing the installation effort. Automatic calibration and cleaning as well as the low consumption of reagents save you operating and maintenance costs. Advanced diagnostics with remote

access ensure process safety and support you in providing process documentation to the authorities.

Lastnosti in specifikacije

Analyser

Merilni princip

Colorimetric

Characteristic

Analyzer for ammonium in aqueous solutions

Measuring method

Comply with standard colorimetric measuring principle - indophenol blue method following ISO 7150-1, DIN 38406-5 and GB 7481-87

Size

Housing (open version):

793 x 530 x 417 mm

31.22 x 20.87 x 16.42 in

Housing (closed version):

793 x 530 x 463 mm

31.22 x 20.87 x 18.23 in

Housing with base:

1723 x 530 x 463 mm

67.83 x 20.87 x 18.23 in

Design

Open design / cabinet:

Plastic ASA-PC

Stand housing:

Plastic ASA-PC, steel coated

Process temperature

4 to 40 °C (39 to 104 °F)

Ambient temperature

5 to 40 °C (41 to 104 °F)

Outdoor version: - 20 to 40 °C (-4 to 104 °F)

Analyser**Process pressure**Unpressurized

Sample flow rateMin. 5 ml/min (0.17 fl.oz/min)

Consistency of the sample

Low solids content

Turbidity < 50 NTU, aqueous, homogenized

Specials

Easy upgrade to measuring station with up to four digital Memosens sensors

Automatic calibration and cleaning

User-configurable measuring, cleaning and calibration intervals

Optional cooling module for longer reagent life time

Automatic calibration and cleaning

Optional 2 channel version

User-definable measuring ranges

Flexibile functionality and modular expandable

Digital communication for remote access

Application

Monitoring and optimization of the cleaning capacity of municipal and industrial wastewater treatment plants

Monitoring of the wastewater treatment plant outlet for documentation purposes

Monitoring and optimization of activated sludge basins

Power supply100 to 120 VAC / 200 to 240 VAC \pm 10%24 VDC \pm 10%50 \pm 1 or 60 \pm 1.2 Hz

Output / communication

2x 0/4 to 20 mA

Optional: Webserver, Modbus, Ethernet/IP, Profibus DP

Analyser

Input

1 or 2 measuring channels
Optional 1 to 4 digital sensor inputs for sensors with Memosens protocol

Measurement range

0.05 to 20 mg/l NH₄-N
0.5 to 50 mg/l NH₄-N
1 to 100 mg/l NH₄-N
0.5 to 50 mg/l with dilution function to maximum 10 to 1000 mg/l NH₄-N

Consumables

Reagents and standard solutions CY80AM
Cleaner CY800
Maintenance kit CAV800

Več informacij www.si.endress.com/CA80AM