

HAW562

Surge arrester

Surge arrester for DIN rail according to IEC 60715



Benefits:

- Investment intensive measuring instruments protected
- Increased plant availability as surge arrester is perfectly matched to the electronic components involved in process automation and process measuring technology
- Application in Ex areas - optionally available with SIL2 intrinsically safe approvals
- Vibration and shock tested according to EN 60068-2
- Direct and indirect shield grounding

from **THB2,302.00**

Price as of 21.10.2021

More information and current pricing:

www.th.endress.com/HAW562

Field of application: The HAW562 surge arrester is used to protect electronic components from being destroyed by overvoltage. It ensures that overvoltage surges which occur in signal cables (e.g. 4 to 20 mA), in communication lines (fieldbuses) and in power lines are safely passed into the ground. The functionality of the transmitter or the electronics component to be protected is not affected.

Features and specifications

Surge arrester

Measuring principle

Surge arrester

Function

Surge arrester for DIN rail mounting

Compact device for an easy ordering (no separation of mounting module and protection module)

Flexible integration into the measuring chains of the process industry due to approvals according to ATEX & IEC, SIL2 conformity

compatibility with the established fieldbusses (HART, FF, PA)

Innovative grounding concept to avoid low-frequency equalizing currents – direct and indirect shield grounding possible in one device

Uninterruptible operation of the plant due to an automatic resetting after the discharge process

Certification

SIL2 conformity

CSA

Surge arrester

Dimensions (wxhxd)

HAW562-AAA, HAW562-AAD, HAW562-AAE, HAW562-8DA:

12 x 90 x 72.5 mm

(0.47" x 3.54" x 2.85")

HAW562-AAB, HAW562-AAC:

18 x 90 x 73 mm

(0.71" x 3.54" x 2.87")

Operating Voltage24V/60V/230V/5V/12(80)V/24V

Surge arrester

Measuring principleSurge arrester

Measuring principleSurge arrester for DIN rail mounting

Function

Surge arresters are applied to protect electronic components of a plant against overvoltage! Due to this investment intensive measuring instruments are protected and the plant availability is increased.

ApplicationSurge protection for power supply or signal / communication cables

SIL2

Surge arrester

Certificates

ATEX

IECEX

CSA

More information www.th.endress.com/HAW562