

Conductive Point level detection Double rod probe 11362Z

High resistant probes for corrosive liquids in plastic vessels



Avantajlar:

- Reliable and safe measurement
- Safe measurement even for applications in explosion hazardous area
- Variable process connections for various applications

Özelliklere genel bakış

- **Process temperature** -40 °C ... 150 °C (-40 °F ... 302 °F)
- **Process pressure / max. overpressure limit** Vacuum ... 30 bar (Vacuum ... 435 psi)
- **Min. conductivity of medium** 20 µS/cm

Uygulama alanı: The 11362Z is a high resistant probe for applications requiring accurate point level detection or overflow prevention in plastic vessels or vessels made of non-conducting material. The two-point control can be carried out in vessels with electrically conducting walls.

Daha fazla bilgi ve güncel fiyatlandırma:

www.tr.endress.com/11362Z

Özellikler ve şartlar

Point Level / Liquids

Measuring principle

Conductive

Characteristic / Application

Double rod probe with high-class media contacting wetted parts

Point Level / Liquids

Supply / Communication

Relay

Ambient temperature

-20 °C ... 80 °C
(-4 °F ... 176 °F)

Process temperature

-40 °C ... 150 °C
(-40 °F ... 302 °F)

Process pressure / max. overpressure limit

Vacuum ... 30 bar
(Vacuum ... 435 psi)

Min. conductivity of medium

20 µS/cm

Main wetted parts

PTFE, PFA, 316 TI, Alloy B/C4, Titan, Tantal, Monel

Process connection

G 1 1/2A
NPT1 1/2"
Flange DIN /ASME

Sensor length

0.1m ... 4m
(4ft ... 157ft)

Communication

Relay

Certificates / Approvals

ATEX, NEPSI

Components

Transmitter: FTW325

Point Level / Liquids

Application limits

Observe min medium conductivity

Ayrıntılı bilgi www.tr.endress.com/11362Z