

## TR25 Modular RTD thermometer

Comprehensive and common temperature measurement technology for almost all branches of industry



Daha fazla bilgi ve güncel fiyatlandırma:

[www.tr.endress.com/TR25](http://www.tr.endress.com/TR25)

### Avantajlar:

- High degree of flexibility thanks to modular design with standard terminal heads as per DIN EN 50446 and customer-specific immersion lengths
- High degree of insert compatibility and design as per DIN 43772
- Fast response time with reduced tip form
- Head transmitter with easy selection: Analog output 4 to 20 mA, HART®, PROFIBUS® PA or FOUNDATION Fieldbus™

### Özelliklere genel bakış

- **Accuracy** class A acc. to IEC 60751 class AA acc. to IEC 60751
- **Response time** depending on configuration  $t_{50} = 2\text{ s}$   $t_{90} = 5\text{ s}$
- **Max. process pressure (static)** at 20 °C: 40 bar (580 psi)
- **Operating temperature range** PT 100: -200 °C ...600 °C (-328 °F ...1.112 °F)
- **Max. immersion length on request** up to 10.000,00 mm (393,70")

**Uygulama alanı:** The thermometer is mainly used in the chemical industry but also finds its use in other branches. The device with head transmitter is a complete unit ready for use with enhanced measurement accuracy and reliability compared to directly wired sensors. A variety of process connections, dimensions and materials offer flexible application possibilities.

### Özellikler ve şartlar

**Thermometer****Measuring principle**Resistance Temperature Detector

---

**Characteristic / Application**

metric style

modular temperature assembly

threaded process connection

without neck

---

**Thermowell / protection tube**without (not intended to use with thermowell)

---

**Insert / probe**mineral insulated (MI), flexible

---

**Outer diameter protection tube / Insert**6,0 mm (0,24")

---

**Max. immersion length on request**up to 10.000,00 mm (393,70")

---

**Material protection tube/ thermowell**1.4404 (316L)

---

**Optional coating**Not defined

---

## Thermometer

**Process connection**

male thread:

G1/4"

G1/2"

NPT1/4"

NPT1/2"

**Tip shape**

straight

reduced

**Surface roughness Ra**

Not defined

**Operating temperature range**

PT 100:

-200 °C ...600 °C

(-328 °F ...1.112 °F)

**Max. process pressure (static)**

at 20 °C: 40 bar (580 psi)

**Accuracy**

class A acc. to IEC 60751

class AA acc. to IEC 60751

---

## Thermometer

### Response time

depending on configuration

$t_{50} = 2 \text{ s}$

$t_{90} = 5 \text{ s}$

---

### Integration head transmitter

yes (4 ... 20 mA; HART; PROFIBUS PA; FOUNDATION  
FIELDBUS)

---

### Certification

Gost Metrology

SIL (transmitter only)

---

Ayrıntılı bilgi [www.tr.endress.com/TR25](http://www.tr.endress.com/TR25)