

# TR63

## Explosion-proof Pt100 Thermometer

Safe monitoring of process temperatures in challenging applications e. g. in the Oil & Gas industry



Daha fazla bilgi ve güncel fiyatlandırma:

[www.tr.endress.com/TR63](http://www.tr.endress.com/TR63)

### Avantajlar:

- Types of protection for use in hazardous locations: Intrinsic safety (Ex i.a.), flameproof (Ex d), non-sparking (Ex nA)
- High degree of flexibility thanks to modular design with standard terminal heads as per DIN EN 50446 and customer-specific immersion lengths
- Optionally fast response time with tapered tip form
- Variable selection of process connections: thread, compression fitting or flange
- Extension neck, nipple union version, to protect the head transmitter from overheating
- Marine approval

### Özelliklere genel bakış

- **Accuracy** class A acc. to IEC 60751 class AA acc. to IEC 60751
- **Response time** depending on configuration  $t_{50} = 4$  s  $t_{90} = 8$  s
- **Max. process pressure (static)** at 20 °C: 100 bar (1.450 psi)
- **Operating temperature range** PT100 TF StrongSens: -50 °C ...500 °C (-58 °F ...932 °F) PT100 WW: -200 °C ...600 °C (-328 °F ...1.112 °F) PT100 TF: -50 °C ...400 °C (-58 °F ...752 °F)
- **Max. immersion length on request** up to 10.000,00 mm (393,70")

**Uygulama alanı:** The robust thermometer is designed for use in demanding and safety relevant applications e.g. in the Chemical, Oil & Gas and Energy industry. Harsh environments, corrosive substances and highest pressures can be handled by the use of robust protection tubes and special materials. An optional head transmitter with all common

communication protocols makes the device ready to use with enhanced measurement accuracy and reliability compared to directly wired sensors. Flexible configuration possible.

## Özellikler ve şartlar

---

### Thermometer

**Measuring principle**

Resistance Temperature Detector

---

**Characteristic / Application**

US style

modular temperature assembly

for heavy duty applications

suitable for hazardous areas

flanged process connection

with neck

incl. thermowell / protection tube (metal)

---

**Thermowell / protection tube**

welded protection tube

---

**Insert / probe**

mineral insulated (MI), flexible

---

## Thermometer

**Outer diameter protection tube / Insert**

1/4" SCH80

1/2" SCH80

1/2" SCH40

3/4" SCH80

3/4" SCH40

**Max. immersion length on request**

up to 10.000,00 mm (393,70")

**Material protection tube/ thermowell**

1.4404 (316)

1.4749 (~446)

**Optional coating**

Not defined

## Thermometer

**Process connection**

male thread:

NPT1/2"

NPT3/4"

NPT1"

flange:

ASME 1" 150 RF (B16.5)

ASME 1" 300 RF (B16.5)

ASME 1" 600 RF (B16.5)

ASME 1,5" 150 RF (B16.5)

ASME 1,5" 300 RF (B16.5)

ASME 1,5" 600 RF (B16.5)

ASME 2" 300 RF (B16.5)

ASME 2" 600 RF (B16.5)

**Tip shape**

straight

reduced

**Surface roughness Ra**

Not defined

---

**Thermometer****Operating temperature range**

PT100 TF StrongSens:

-50 °C ...500 °C

(-58 °F ...932 °F)

PT100 WW:

-200 °C ...600 °C

(-328 °F ...1.112 °F)

PT100 TF:

-50 °C ...400 °C

(-58 °F ...752 °F)

---

**Max. process pressure (static)**

at 20 °C: 100 bar (1.450 psi)

---

**Accuracy**

class A acc. to IEC 60751

class AA acc. to IEC 60751

---

**Response time**

depending on configuration

t<sub>50</sub> = 4 st<sub>90</sub> = 8 s

---

**Integration head transmitter**yes (4 ... 20 mA; HART; PROFIBUS PA; FOUNDATION  
FIELDBUS)

Thermometer

**Ex - approvals**

ATEX II

IECEX

NEPSI

EAC Ex

Explosion proof

---

**Certification**

Gost Metrology

SIL (transmitter only)

Marine approval

---

Ayrıntılı bilgi [www.tr.endress.com/TR63](http://www.tr.endress.com/TR63)