

# Turbidity and suspended solids sensor Turbimax CUS50D

## Memosens sensor for turbidity, suspended solids and absorption measurement



Daha fazla bilgi ve güncel fiyatlandırma:

[www.tr.endress.com/CUS50D](http://www.tr.endress.com/CUS50D)

### Avantajlar:

- High level of measurement accuracy and repeatability for stable measurements – in the middle and high turbidity measuring range
- High chemical resistance, low maintenance required: Sensor head consists completely of a dirt-repellent Teflon derivative.
- The robust plastic version of the sensor is designed for the use in corrosive media or saltwater.
- Fast and easy commissioning: Sensor comes pre-calibrated, includes various application models and can easily be adjusted via single-point-calibration.
- Automatic sludge model independently selects the optimum signal path for every sludge type.
- Perfect process adaption: Fast sensor positioning with a large variety of Endress+Hauser assemblies.

### Özelliklere genel bakış

- **Measurement range** 40 to 4 000 FAU 0 to 60 g/L suspended solids 0 to 10 OD
- **Process temperature** Process temperature -20 to 85 °C (-4 to 185 °F) Ambient temperature -20 to 60 °C (-4 to 140 °F)
- **Process pressure** 0.5 to 4.5 bar (7.3 to 65.3 psi) absolute

**Uygulama alanı:** Turbimax CUS50D is a smart sensor that allows unattended operation in a wide range of industrial wastewater and process applications. Its absorption principle enables single-point-calibration. Choose from different integrated analytical models to adapt the sensor to your specific application. With Memosens digital technology, Turbimax CUS50D combines maximum process and data

integrity with simple operation. It resists corrosion and enables lab calibration.

## Özellikler ve şartlar

### Turbidity

**Measuring principle**

Absorption

**Application**

Absorption sensor for turbidity and suspended solids measurements in industrial wastewater and processes

**Installation**

Insitu (immersion in process or retractable assembly)

**Measurement range**

40 to 4 000 FAU

0 to 60 g/L suspended solids

0 to 10 OD

**Measuring principle**

Absorption

**Design**

40 mm sensor

**Material**

Sensor head: PCTFE

Sensor shaft: 1.4571 stainless steel (316TI) or plastic (PPS GF40)

O-ring: EPDM

**Dimension**

209.5 x 40 mm (8.25 x 1.57 inch)

**Process temperature**

Process temperature -20 to 85 °C (-4 to 185 °F)

Ambient temperature -20 to 60 °C (-4 to 140 °F)

## Turbidity

### Process pressure

0.5 to 4.5 bar (7.3 to 65.3 psi) absolute

---

### Connection

G1, NPT3/4

---

### Ingres protection

IP68

---

Ayrıntılı bilgi [www.tr.endress.com/CUS50D](http://www.tr.endress.com/CUS50D)