

## iTHERM ModuLine TM121

Thermometer with RTD or TC insert complete with manufactured thermowell produced from pipe material



Fiyatı en az **€80,22**

23.09.2021 tarihinden itibaren fiyat

Daha fazla bilgi ve güncel fiyatlandırma:

[www.tr.endress.com/TM121](http://www.tr.endress.com/TM121)

### Avantajlar:

- Economical, reliable measurement
- User-friendly from product selection to maintenance
- Wide range of process connections
- Easy and safe device setup and service using Bluetooth® communication

### Özelliklere genel bakış

- **Accuracy** Class A acc. to IEC 60751 Class B acc. to IEC 60751 Class standard acc. to ASTM E230 Class 2 acc. to IEC 60584-2
- **Response time** t90 around 100 s depending on configuration
- **Max. process pressure (static)** depending on the configuration
- **Operating temperature range** Basic PT100 TF: -50 °C ...200 °C (-58 °F ...392 °F) Thermocouple: Typ K up to 600 °C (1.112 °F)
- **Max. immersion length on request** up to 1.000,0 mm (39")

**Uygulama alanı:** RTD or TC assembly characterized by basic sensor technology, application in non-hazardous areas, standard extension neck, low-cost unit. The devices are available with optional Bluetooth®-enabled head transmitters with 4 to 20 mA output or HART® communication, providing enhanced measurement accuracy and reliability compared to directly wired sensors.

### Özellikler ve şartlar

Thermometer

Measuring principle

Resistance Temperature Detector

---

**Thermometer****Characteristic / Application**

metric style

modular temperature assembly

universal range of application

with neck

incl. thermowell / protection tube (metal)

---

**Thermowell / protection tube**

welded protection tube or to be used with thermowell

---

**Insert / probe**

Basis Sensortechnologie

---

**Outer diameter protection tube / Insert**

Thermowell:

9x1,25 mm

11x2 mm

---

**Max. immersion length on request**

up to 1.000,0 mm (39")

---

**Material protection tube/ thermowell**

316L (1.4404)

---

## Thermometer

**Process connection**

Thread:

G1/2"

NPT1/2"

M20x1.5, M27x2, M33x2

Compression fitting:

NPT1/2", G1/2", G1"

Flansche:

DN25 DN40 B1

ASME 1" 150 RF

ASME 1" 300 RF

ASME 1 1/2" 150 RF

ASME 2" 150 RF

ASME 2" 300 RF

---

**Tip shape**straight

---

## Thermometer

### Operating temperature range

Basic PT100 TF:

-50 °C ...200 °C

(-58 °F ...392 °F)

Thermocouple:

Typ K up to 600 °C (1.112 °F)

---

### Max. process pressure (static)

depending on the configuration

---

### Accuracy

Class A acc. to IEC 60751

Class B acc. to IEC 60751

Class standard acc. to ASTM E230

Class 2 acc. to IEC 60584-2

---

### Response time

t<sub>90</sub> around 100 s

depending on configuration

---

### Integration head transmitter

yes (4 ... 20 mA; HART)

---

Ayrıntılı bilgi [www.tr.endress.com/TM121](http://www.tr.endress.com/TM121)