

Vibronic

Point level detection

Liquiphant FTL85

Coated point level switch for liquids for FailSafe overfill prevention



Daha fazla bilgi ve güncel fiyatlandırma:

www.tr.endress.com/FTL85

Avantajlar:

- Use in safety systems requiring functional safety to SIL3 in accordance with IEC 61508 Ed.2.0/ IEC 61511-1/ISA 84-1 and DIN EN ISO 13849
- Proof test: proof testing interval up to 12 years, Slave devices tested at the press of a button
- Permanent self-monitoring/internal redundancy
- 4-20mA interface (acc. to NAMUR NE 06/NE 43): easy integration via the switching unit (Nivotester FailSafe FTL825) with a two-channel output (safety contacts) and locking function or direct integration into a safety PLC
- No adjustment: quick, low-cost startup
- No mechanically moving parts: no maintenance, no wear, long operating life
- Monitoring of fork for damage, corrosion, buildup and mechanical blocking

Özelliklere genel bakış

- **Process temperature** $-50^{\circ}\text{C} \dots +150^{\circ}\text{C}$ ($-58^{\circ}\text{F} \dots +300^{\circ}\text{F}$)
- **Process pressure absolute / max. overpressure limit**
Vacuum...40 bar (580 psi)
- **Min. density of medium** Density from 0.4 g/cm³ (0.4 SGU)

Uygulama alanı: Liquiphant FTL85 is a coated point level switch for use in hazardous areas with all international certificates. FailSafe overfill prevention in applications with functional safety up to SIL3 with one device. With high corrosion-resistant coating made of enamel, ECTFE and various PFA materials. Reliable measurement values, not affected by:

changing media properties, flow, turbulences, gas bubbles, foam, vibrations or build-up.

Özellikler ve şartlar

Point Level / Liquids

Measuring principle

Vibration Liquids

Characteristic / Application

Coated point level switch for MIN and MAX safety applications up to SIL3,
Dual Sealing/ Second line of defense,
Modular housing concept

Specialities

Outstanding features:

- permanent LIVE signal monitors function safety
- failsafe design and
- high availability of the measuring values

Supply / Communication

2-wire 4...20 mA

Ambient temperature

-50°C...+70°C
(-58°F...+160°F)

Process temperature

-50°C...+150°C
(-58°F...+300°F)

Process pressure absolute / max. overpressure limit

Vacuum...40 bar
(580 psi)

Min. density of medium

Density from 0.4 g/cm³
(0.4 SGU)

Point Level / Liquids

Main wetted parts

With high corrosion-resistant coating made of enamel, ECTFE and various PFA materials

Process connection

Flange:
DN25...DN100,
ASME 1"...4",
JIS 10K...20K

Sensor length

Extension pipe up to 3 m (9.8 ft)

Communication

2-wire 4...20 mA

Certificates / Approvals

ATEX, FM, CSA, CSA C/US, IEC Ex, NEPSI, EAC

Safety approvals

Overfill protection WHG
Leakage Detection
SIL3

Options

AlloyC Material
PWIS free
Pressure tight feed through
Weather protection

Components

Nivotester FTL825, Transmitter

Ayrıntılı bilgi www.tr.endress.com/FTL85