

## RTD Thermometer TST414



More information and current pricing:

[www.uk.endress.com/TST414](http://www.uk.endress.com/TST414)

### Benefits:

- High degree of flexibility thanks to modular design with standard terminal heads as per DIN EN 50446 and customer-specific immersion lengths
- High degree of insert compatibility and design as per DIN 43772
- Fast response time

### Specs at a glance

- **Accuracy** class A acc. to IEC 60751 class B acc. to IEC 60751
- **Response time**  $t_{50} = 10\text{ s}$   $t_{90} = 30\text{ s}$
- **Max. process pressure (static)** at 20 °C: 50 bar (725 psi)
- **Operating temperature range** PT 100: -50 °C ...400 °C (-58 °F ...752 °F)
- **Max. immersion length on request** up to 10.000,00 mm (393,70")

**Field of application:** The thermometer is mainly used in the chemical industry but also finds its use in other branches. Typical applications are processes where no strong flow is present. The device is supplied with a pocket which protects it from chemical corrosion and allows an easy replacement of the thermometer.

### Features and specifications

Thermometer

**Measuring principle**

Resistance Temperature Detector

---

**Thermometer****Characteristic / Application**

metric style  
modular temperature assembly  
fast response time  
threaded process connection  
without neck  
incl. thermowell / protection tube  
(metal)  
mini-head

---

**Thermowell / protection tube**

welded protection tube

---

**Insert / probe**

mineral insulated (MI), flexible

---

**Outer diameter protection tube / Insert**

4,5 mm (0,18")

---

**Max. immersion length on request**

up to 10.000,00 mm (393,70")

---

**Material protection tube/ thermowell**

1.4571 (316Ti)

---

**Process connection**

male thread:  
G1/2"

---

**Tip shape**

straight

---

**Surface roughness Ra**

1,6 µm (63,0 µin.)

---

**Operating temperature range**

PT 100:  
-50 °C ...400 °C  
(-58 °F ...752 °F)

## Thermometer

---

**Max. process pressure (static)**  
at 20 °C: 50 bar (725 psi)

---

**Accuracy**  
class A acc. to IEC 60751  
class B acc. to IEC 60751

---

**Response time**  
t<sub>50</sub> = 10 s  
t<sub>90</sub> = 30 s

---

**Integration head transmitter**  
no

---

More information [www.uk.endress.com/TST414](http://www.uk.endress.com/TST414)