

TA560

Barstock thermowell

Made of drilled barstock material. Mainly used in heavy duty or general purpose applications.



More information and current pricing:

www.uk.endress.com/TA560

Benefits:

- The extension and the immersion lengths as well as the bar dimensions can be chosen according to process requirements
- A wide choice of standard diameters and materials is available; other versions can be ordered according to specification
- Different grades of surface finishing are also available
- The process connection is threaded. The thermowell stem shape can be straight or conical

Specs at a glance

- **Max. process pressure (static)** 500 bar (7252 psi)
- **Maximum standard immersion length** 900 mm (35,43")
- **Max. immersion length on request** 5.000 mm (196,85")

Field of application: Due to the challenging process conditions by heavy duty applications the load capacity of a thermowell must be calculated exactly. Dye penetration tests, ultrasound test, helium leakage test, pressure endurance test as well as various, non-destructive material tests prove the quality of materials and processing.

Features and specifications

Thermowell

Measuring principle

Bar stock Thermowell

Thermowell

Characteristic / Application

metric style

threaded process connection

hexagonal extension

Head connection

internal thread:

1/2" NPT

Maximum standard immersion**length**

900 mm (35,43")

Max. immersion length on request

5.000 mm (196,85")

Process connection

thread:

3/4" NPT

Thermowell root diameter

20 mm (0,79")

22 mm (0,87")

Medium contact material

1.4401 (316)

1.4404 (316L)

1.4571 (316Ti)

Thermowell

Wetted part finishing (Ra)

< 0,8 µm (31,50 µin)

< 1,6 µm (63,00 µin)

Tip shape

straight

conical

Temperature range

-200...700 °C (-328...1.292 °F)

Max. process pressure (static)

500 bar (7252 psi)

Max. process pressure at 400 °C

300 bar (4351 psi)

More information www.uk.endress.com/TA560