

# 8-channel transmitter

## Liquiline CM448

Flexible multiparameter field device for all industries



More information and current pricing:

[www.uk.endress.com/CM448](http://www.uk.endress.com/CM448)

### Benefits:

- **Clever simplicity:**  
One controller for all parameters and applications, intuitive user interface, automatic sensor recognition, hot plug & play with pre-calibrated Memosens sensors.
- **Complete package:**  
8 channels in one device provide the highest flexibility for every measuring task.
- **Seamless system integration:**  
Unique portfolio of communication standards suits every distributed control system (DCS).
- **Simple and safe commissioning:**  
Saving configuration on SD card enables fast set-up on duplicate installations.
- **Process control from a distance:**  
Integrated web server that allows the operator to remotely view diagnostic data, perform configurations, or access device parameters in any web browser - even via Smartphone.
- **Higher availability, lower costs:**  
Heartbeat Technology enables status-oriented maintenance and easy verification of the entire measuring point and helps to carry out optimization measures.

### Specs at a glance

- **Input** 1 to 8x Memosens digital input 2x 0/4 to 20mA Input optional 2 to 4x Digital input optional

**Output / communication** 2 to 8x 0/4 to 20 mA current outputs, alarmrelay 4x relay, ProfibusDP, Modbus RS485, Modbus TCP, Ethernet

- **Ingres protection** IP66 / IP67

**Field of application:** Liquiline CM448 is a digital multiparameter transmitter for process monitoring and controlling in any application. The 8-channel controller saves you time and money by offering seamless system integration, simple operation and a reduced need for spare part stock. Adapt the controller exactly to your measuring task and connect 1 to 8 sensors as desired. Liquiline CM448 provides you with all the benefits of a best-in-class transmitter platform from clever simplicity to maximum process safety.

## Features and specifications

### Analyser

#### Measuring principle

Potentiometric / ISE

#### Characteristic

Robust plastic housing  
All non-ex applications

#### Process temperature

-20 to 55 °C (0 to 130 °F)

#### Application

Modular 4 wire controller  
Multichannel: 1 to 8 digital channels for Memosens protocol  
Multiparameter: pH, redox, ISFET, conductivity inductive and conductive, dissolved oxygen, nitrate and turbidity  
8 sensors connectable in any combination  
Functionality modular extendable at any time  
Plug and play for modules and sensors

---

## Analyser

**Output / communication**

2 to 8x 0/4 to 20 mA current outputs, alarmrelay  
4x relay, ProfibusDP, Modbus RS485, Modbus TCP, Ethernet

---

**Input**

1 to 8x Memosens digital input  
2x 0/4 to 20mA Input optional  
2 to 4x Digital input optional

---

## Disinfection

**Measuring principle**

Free chlorine

---

**Application**

Modular 4 wire controller  
Multichannel: 1 to 8 digital channels for Memosens protocol  
Multiparameter: pH, redox, ISFET, conductivity inductive and conductive, dissolved oxygen, nitrate and turbidity  
8 sensors connectable in any combination  
Functionality modular extendable at any time  
Plug and play for modules and sensors

---

**Characteristic**

Robust plastic housing  
All non-ex applications

---

**Design**

8x Memosens input, 2 to 8x current output,  
Alarmrelay, 2x relay, SD card for software update and copy & paste of setup

---

**Material**

Housing base: PC-FR  
Housing seal EPDM

---

**Dimension**

237 x 194 x 162 mm  
9.33 x 7.64 x 6.38 inch

---

---

## Disinfection

---

### Process temperature

-20 to 55 °C (0 to 130 °F)

---

### Input

1 to 8x Memosens digital input  
2x 0/4 to 20mA Input optional  
2 to 4x Digital input optional

---

### Output / communication

2 to 8x 0/4 to 20 mA current outputs, alarmrelay  
4x relay, ProfibusDP, Modbus RS485, Modbus TCP, Ethernet

---

### Additional certifications

EAC, cCSAus

---

## ORP / Redox

---

### Measuring principle

Sensor ORP / Redox

---

### Application

Modular 4 wire controller  
Multichannel: 1 to 8 digital channels for Memosens protocol  
Multiparameter: pH, redox, ISFET, conductivity inductive and conductive, dissolved oxygen, nitrate and turbidity  
8 sensors connectable in any combination  
Functionality modular extendable at any time  
Plug and play for modules and sensors

---

### Characteristic

Robust plastic housing  
All non-ex applications

---

### Design

8x Memosens input, 2 to 8x current output,  
Alarmrelay, 2x relay, SD card for software update and copy & paste of setup

---

## ORP / Redox

**Material**

Housing base: PC-FR

Housing seal EPDM

---

**Dimension**

237 x 194 x 162 mm

9.33 x 7.64 x 6.38 inch

---

**Process temperature**

-20 to 55 °C (0 to 130 °F)

---

**Ingres protection**

IP66 / IP67

---

**Input**

1 to 8x Memosens digital input

2x 0/4 to 20mA Input optional

2 to 4x Digital input optional

---

**Output / communication**

2 to 8x 0/4 to 20 mA current outputs, alarmrelay

4x relay, ProfibusDP, Modbus RS485, Modbus TCP, Ethernet

---

**Additional certifications**

EAC, cCSAus

---

## Oxygen

**Measuring principle**

Amperometric oxygen measurement

---

**Application**

Modular 4 wire controller

Multichannel: 1 to 8 digital channels for Memosens protocol

Multiparameter: pH, redox, ISFET, conductivity inductive and conductive, dissolved oxygen, nitrate and turbidity

8 sensors connectable in any combination

Functionality modular extendable at any time

Plug and play for modules and sensors

---

## Oxygen

---

### Characteristic

Robust plastic housing  
All non-ex applications

---

### Design

8x Memosens input, 2 to 8x current output,  
Alarmrelay, 2x relay, SD card for software update and copy & paste of  
setup

---

### Material

Housing base: PC-FR  
Housing seal EPDM

---

### Dimension

237 x 194 x 162 mm  
9.33 x 7.64 x 6.38 inch

---

### Process temperature

-20 to 55 °C (0 to 130 °F)

---

### Input

1 to 8x Memosens digital input  
2x 0/4 to 20mA Input optional  
2 to 4x Digital input optional

---

### Output / communication

2 to 8x 0/4 to 20 mA current outputs, alarmrelay  
4x relay, ProfibusDP, Modbus RS485, Modbus TCP, Ethernet

---

### Additional certifications

EAC, cCSAus

---

## Turbidity

---

### Measuring principle

Single beam scattered light

---

## Turbidity

### Application

Modular 4 wire controller

Multichannel: 1 to 8 digital channels for Memosens protocol

Multiparameter: pH, redox, ISFET, conductivity inductive and conductive, dissolved oxygen, nitrate and turbidity

8 sensors connectable in any combination

Functionality modular extendable at any time

Plug and play for modules and sensors

### Characteristic

Robust plastic housing

All non-ex applications

### Design

8x Memosens input, 2 to 8x current output,

Alarmrelay, 2x relay, SD card for software update and copy & paste of setup

### Material

Housing base: PC-FR

Housing seal EPDM

### Dimension

237 x 194 x 162 mm

9.33 x 7.64 x 6.38 inch

### Process temperature

-20 to 55 °C (0 to 130 °F)

### Ingres protection

IP66 / IP67

### Input

1 to 8x Memosens digital input

2x 0/4 to 20mA Input optional

2 to 4x Digital input optional

## Turbidity

### Output / communication

2 to 8x 0/4 to 20 mA current outputs, alarmrelay  
4x relay, ProfibusDP, Modbus RS485, Modbus TCP, Ethernet

---

### Additional certifications

EAC, cCSAus

---

## Conductivity

### Measuring principle

Potentiometric

---

### Application

Modular 4 wire controller  
Multichannel: 1 to 8 digital channels for Memosens protocol  
Multiparameter: pH, redox, ISFET, conductivity inductive and conductive, dissolved oxygen, nitrate and turbidity  
8 sensors connectable in any combination  
Functionality modular extendable at any time  
Plug and play for modules and sensors

---

### Characteristic

Robust plastic housing  
All non-ex applications

---

### Design

8x Memosens input, 2 to 8x current output,  
Alarmrelay, 2x relay, SD card for software update and copy & paste of setup

---

### Material

Housing base: PC-FR  
Housing seal EPDM

---

### Dimension

237 x 194 x 162 mm  
9.33 x 7.64 x 6.38 inch

---



---

## Conductivity

**Ingres protection**

IP66 / IP67

---

**Input**

1 to 8x Memosens digital input

2x 0/4 to 20mA Input optional

2 to 4x Digital input optional

---

**Output / communication**

2 to 8x 0/4 to 20 mA current outputs, alarmrelay

4x relay, ProfibusDP, Modbus RS485, Modbus TCP, Ethernet

---

**Additional certifications**

EAC, cCSAus

---

## pH

**Measuring principle**

Potentiometric

---

**Application**

Modular 4 wire controller

Multichannel: 1 to 8 digital channels for Memosens protocol

Multiparameter: pH, redox, ISFET, conductivity inductive and conductive, dissolved oxygen, nitrate and turbidity

8 sensors connectable in any combination

Functionality modular extendable at any time

Plug and play for modules and sensors

---

**Characteristic**

Robust plastic housing

All non-ex applications

---

**Design**

8x Memosens input, 2 to 8x current output,

Alarmrelay, 2x relay, SD card for software update and copy &amp; paste of setup

pH

**Material**

Housing base: PC-FR

Housing seal EPDM

**Dimension**

237 x 194 x 162 mm

9.33 x 7.64 x 6.38 inch

**Process temperature**

-20 to 55 °C (0 to 130 °F)

**Ingres protection**

IP66 / IP67

**Input**

1 to 8x Memosens digital input

2x 0/4 to 20mA Input optional

2 to 4x Digital input optional

**Output / communication**

2 to 8x 0/4 to 20 mA current outputs, alarmrelay

4x relay, ProfibusDP, Modbus RS485, Modbus TCP, Ethernet

**Additional certifications**

EAC, cCSAus

More information [www.uk.endress.com/CM448](http://www.uk.endress.com/CM448)