

# RIA46

## Field meter with control unit

Multifunctional field meter for monitoring and indication of analog measured values



from **\$457.00**

Price as of 05/12/2021

More information and current pricing:

[www.us.endress.com/RIA46](http://www.us.endress.com/RIA46)

### Benefits:

- 5-digit 7-segment LC display, backlit
- 1 or 2 universal inputs
- 2 relays (optional)
- Min./max. value saved
- 1 or 2 calculated values and linearization table
- Digital status output (Open Collector)
- SIL 2 approval (optional)

### Specs at a glance

- **Input** 2 x universal (U, I, R, RTD, TC)
- **Output** 2 x analogue output (I, U) 1 x loop power supply
- **Output** 2 x analogue output (I, U) 1 x loop power supply
- **Display** Multicolor backlight LCD White/black/yellow Bargraph  
Unit TAG Alarm warning in plain text
- **Power Supply** 20...250V AC/DC

**Field of application:** Analog measured values are indicated, evaluated and calculated by the field indicator. With the integrated loop power supply two-wire sensors can be powered. The universal inputs enable the connection of current, voltage, RTDs and TCs. Limit values can be monitored and relays can be switched. Via analog outputs process signals can be forwarded. The integrated application package "differential pressure" allows the quick and easy commissioning for differential pressure applications.

### Features and specifications

---

Process indicator & control units

**Measuring principle**

Indicators with control unit

---

**Measuring principle**

Field meter with control unit

---

**Function**

Display

Loop Power Supply

Transmitter Functionality

Barrier

Signal Isolation

Calculation

Limit Alarm

---

**Display**

Multicolor backlight LCD

White/black/yellow

Bargraph

Unit

TAG

Alarm warning in plain text

---

**Power Supply**

20...250V AC/DC

---

**Process indicator & control units****Input**

2 x universal (U, I, R, RTD, TC)

---

**Output**

2 x analogue output (I, U) 1 x loop power supply

---

**Output**

2 x analogue output (I, U) 1 x loop power supply

---

**Software functions**

Linearization

Minimum value per channel

Maximum value per channel

Calculation

Band value monitoring

---

**Certificates**

ATEX II (1) GD [Ex ia] 4C

CSA AIS

NI/I/2 ABCDEFG/T4

FM AIS

NI/I/2 ABCDEFG/T4

---

**SIL**

2

---

**Panel mounting**

field

---

## Acquisition / Evaluation

**Measuring principle**Display

---

**Function**

Display

Loop Power Supply

Transmitter Functionality

Barrier

Signal Isolation

Calculation

Limit Alarm

---

**Certification**

ATEX II (1) GD [Ex ia] 4C

CSA AIS

NI/I/2 ABCDEFG/T4

FM AIS

NI/I/2 ABCDEFG/T4

UR C/US

---

**Input**2 x universal (U, I, R, RTD, TC)

---

**Output**

2 x analogue output (I, U)

1 x loop power supply

---

**Acquisition / Evaluation****Relay output**

2 x changeover contact

1 x open collector

---

**Auxiliary power supply / Loop power supply**20...250V AC/DC

---

**Dimensions (wxhxd)**

Field housing:

199 x 133 x 96 mm

(7.83" x 5.24" x 3.78")

---

**Software**

Linearization

Minimum value per channel

Maximum value per channel

Calculation

Band value monitoring

---

**Operation**

3 keys

Interface CDI to USB at PC + configuration software

FieldCare

---

Acquisition / Evaluation

**Display**

Multicolor backlight LCD

White/black/yellow

Bargraph

Unit

TAG

Alarm warning in plain text

---

More information [www.us.endress.com/RIA46](http://www.us.endress.com/RIA46)