

## Multiparameter handheld Liquiline To Go CYM290

Portable device for pH/ORP, conductivity, oxygen and temperature measurement in all industries



More information and current pricing:

[www.za.endress.com/CYM290](http://www.za.endress.com/CYM290)

### Benefits:

- Make the right decisions for your process: the handheld's reliable measurements with 100% signal integrity help you to take the appropriate action at the right moment.
- Trust your grab sample values: using the same technology for process and grab sample measurement provides you with full consistency.
- Take it to any measuring point: the robust, shock-proof housing with ingress protection to IP66/67 enables fast process control even in the most challenging environments.
- Simplify your daily work: hot plug & play with pre-calibrated Memosens sensors enables you to rapidly change from one parameter to another.

### Specs at a glance

- **Input** M8 contact for Memosens lowpower protocol, one channel instrument
- **Output / communication** N/a
- **Ingress protection** IP 66/67

**Field of application:** With Liquiline To Go CYM290 you get the information you need, where you need it. The robust multiparameter handheld enables you to control any measuring point in your plant with the identical Memosens sensors that you use in your process. This guarantees full data consistency between your measurements with results you can trust: reliable measuring values that allow you to quickly take any remedial actions necessary to keep your process running under optimal conditions.

---

## Features and specifications

---

pH

**Measuring principle**

Potentiometric

---

**Application**

for field laboratory use

---

**Installation**

portable instrument

---

**Characteristic**

handheld instrument for pH, conductivity and dissolved oxygen  
Memosens sensors

---

**Measuring principle**

pH, conductivity and dissolved oxygen Memosens sensors

---

**Design**

portable handheld

---

**Material**

PA 12, GF30 + TP

---

**Dimension**

approx. (132 x156 x 30) mm

---

**Ex certification**

no

---

**Ingres protection**

IP 66/67

---

**Input**

M8 contact for Memosens lowpower protocol, one channel instrument

---

**Output / communication**

N/a

---

Conductivity

**Measuring principle**  
Amperometric oxygen  
measurement

---

Oxygen

**Measuring principle**  
Amperometric oxygen  
measurement

---

More information [www.za.endress.com/CYM290](http://www.za.endress.com/CYM290)