

RID14

8 channel field indicator for fieldbuses

Indication of up to 8 process or calculated values for FOUNDATION Fieldbus™ or PROFIBUS® PA protocol



from **ZAR12,778.00**

Price as of 28.05.2022

More information and current pricing:

www.za.endress.com/RID14

Benefits:

- Simple and standardized communication via fieldbus protocol
- Listener mode for up to 8 input channels or digital status
- Brilliant, backlit LC display with bar graph, diagnostic symbols and clear text field
- No external power supply required
- International approvals

Specs at a glance

- **Input** Foundation Fieldbus protocol PROFIBUS PA protocol
- **Output** Not defined
- **Display** High contrast backlit LCD with bargraph TAG/unit
- **Power Supply** Not defined

Field of application: The 8 channel indicator shows measured and calculated values and status information of the fieldbus users in a FOUNDATION Fieldbus™ or PROFIBUS® PA network. In the listener mode the device listens to the set fieldbus addresses and indicates their values. In addition, for FOUNDATION Fieldbus™ values available on the bus can be indicated via function block interconnection. A plain text field allows the display of the engineering unit or of the TAG. A bar graph is available for trend visualization.

Features and specifications

Acquisition / Evaluation**Measuring principle**Display

Function

Display values

Advanced diagnostic

Certification

ATEX Ex ia

ATEX Ex d

FM

CSA

IECEX Ex ia

IECEX Ex d

IECEX Ex tD

Input

Foundation Fieldbus protocol

PROFIBUS PA protocol

Dimensions (wxhxd)

Field housing:

132 x 135 x 106 mm

(5.2" x 5.31" x 4.17")

Software

Listener Mode

On Foundation Fieldbus also function block connection:

Display transducer block

Advanced diagnostic block´

2 x input selector

Arithmetic block

Integrator block

PID block

Acquisition / Evaluation

Operation

Foundation Fieldbus: via fieldbus
 PROFIBUS PA: DTM and FieldCare or DIP-switches on the device
 Write lock on hardware

Display

High contrast backlit LCD with bargraph
 TAG/unit

Operating Voltage

9-32 V DC, polarity independent

Process indicator & control units

Measuring principle

Fieldbus indicators

Measuring principle

8 channel field indicator for fieldbuses

Function

Display values
 Advanced diagnostic

Display

High contrast backlit LCD with bargraph
 TAG/unit

Power Supply

Not defined

Input

Foundation Fieldbus protocol
 PROFIBUS PA protocol

Output

Not defined

Process indicator & control units**Output**

Not defined

Software functions

Listener Mode

On Foundation Fieldbus also function block connection:

Display transducer block

Advanced diagnostic block

2 x input selector

Arithmetic block

Integrator block

PID block

Certificates

ATEX Ex ia

ATEX Ex d

FM

CSA

IECEX Ex ia

IECEX Ex d

IECEX Ex tD

SIL

Not defined

Panel mounting

field

More information www.za.endress.com/RID14