

RB223

Loop powered passive barrier

One or two-channel barrier for the safe separation of 4...20 mA standard signal circuits



from **ZAR2,249.00**

Price as of 28.05.2022

More information and current pricing:

www.za.endress.com/RB223

Benefits:

- Compact side-by-side housing for DIN rail
- Space-saving one-channel and two-channel version
- No power supply necessary
- International Ex approvals; Can be used up to SIL 3
- Bidirectional HART[®] transmission
- Communication sockets for HART[®] + integrated HART[®] resistor for sensor configuration

Specs at a glance

- **Input** 2 x analog 4...20 mA
- **Output** 2 x analog 4...20 mA

Field of application: The RB223 passive barrier can be used to galvanically isolate active signal circuits (0 to 20 mA) in three applications: Transmission from non-Ex to Ex areas e.g for active adjusters, controllers or indicators, Transmission from Ex to non-Ex areas for connection of active, intrinsically safe circuits to the PLC, Transmission from Ex to non-Ex areas for supply of intrinsically safe transmitters with non-intrinsically safe transmitter power supply.

Features and specifications

Power supplies & barrier

Measuring principle

Passive barrier

Power supplies & barrier**Measuring principle**Power supply

FunctionPassive barrier for safe separation of 4...20 mA current circuit

Loop power supplyLoop powered

Auxiliary power supply / Loop power supplyLoop powered

Input2 x analog 4...20 mA

Output2 x analog 4...20 mA

CertificatesCSA GP
ATEX Ex ia
CSA IS
CSA NI
SIL

OperationHART

Acquisition / Evaluation**Measuring principle**Power supply

FunctionPassive barrier for safe separation of 4...20 mA current circuit

Acquisition / Evaluation

Certification

CSA GP
ATEX Ex ia
CSA IS
CSA NI
SIL

Input

2 x analog 4...20 mA

Output

2 x analog 4...20 mA

Auxiliary power supply / Loop power supply

Loop powered

Dimensions (wxhxd)

22.5 x 110 x 112 mm
(0.89" x 4.33" x 4.41")

Operation

HART

More information www.za.endress.com/RB223